


RIF-4-BSC/3X21 - Relay base



2900960

<https://www.phoenixcontact.com/us/products/2900960>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RIF-4... relay base, for high-power relay with 2 or 3 changeover contacts or 3 N/O contacts, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5

Commercial data

Item number	2900960
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	C465
Product key	CK6515
Catalog page	Page 311 (C-5-2019)
GTIN	4046356733182
Weight per piece (including packing)	95.65 g
Weight per piece (excluding packing)	89.5 g
Customs tariff number	85366990
Country of origin	CN

RIF-4-BSC/3X21 - Relay base



2900960

<https://www.phoenixcontact.com/us/products/2900960>

Technical data

Product properties

Product type	Relay socket
Product family	RIFLINE complete

Data management status

Article revision	03
------------------	----

Electrical properties

Nominal voltage U_N	440 V AC
	250 V DC
Nominal current I_N	max. 13 A (Depends on application/assembly)
Protective circuit	depending on the selected input/suppressor modules

Connection data

Connection method	Screw connection
Stripping length	8 mm
Conductor cross section rigid	0.5 mm ² ... 4 mm ²
Conductor cross-section rigid (2 conductors with same cross section)	0.5 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.5 mm ² ... 4 mm ²
	0.5 mm ² ... 4 mm ² (Ferrule with plastic sleeve)
Conductor cross section flexible (2 conductors with same cross section)	0.5 mm ² ... 2.5 mm ²
	0.5 mm ² ... 1.5 mm ² (TWIN ferrule with plastic sleeve)
Conductor cross section AWG	20 ... 10 (solid)
	20 ... 12 (flexible)
Tightening torque	0.5 Nm ... 0.6 Nm

Dimensions

Width	44 mm
Height	96 mm
Depth Retaining bracket	91 mm (with retaining bracket)

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V2 (Housing)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (Depends on application/assembly)
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Approvals

RIF-4-BSC/3X21 - Relay base



2900960

<https://www.phoenixcontact.com/us/products/2900960>

Corrosive gas test

Identification	ISA-S71.04. G3 Harsh Group
	EN 60068-2-60

Mounting

Mounting type	DIN rail mounting
Mounting position	any

RIF-4-BSC/3X21 - Relay base



2900960

<https://www.phoenixcontact.com/us/products/2900960>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2900960>



CSA

Approval ID: 76787



UL Recognized

Approval ID: FILE E 113228



EAC

Approval ID: RU D-DE.B*00573/18



DNV GL

Approval ID: TAA000018V

RIF-4-BSC/3X21 - Relay base



2900960

<https://www.phoenixcontact.com/us/products/2900960>

Classifications

ECLASS

ECLASS-11.0	27371603
ECLASS-12.0	27371603
ECLASS-13.0	27371603

ETIM

ETIM 9.0	EC001456
----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

RIF-4-BSC/3X21 - Relay base



2900960
<https://www.phoenixcontact.com/us/products/2900960>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com