




REV	DATE	MODIFICATION	DRAWN
2013/09/05			

SPECIFICATIONS
1 ELECTRICAL:
UL APPLICATIONS: 250 VOLTS AC MAX., AT 2 AMPS.
DIELECTRIC WITHSTANDING VOLTAGE: 1000 VOLTS AC.
WITHSTAND VOLTAGE TIME: 60S.
INSULATION RESISTANCE: 100 MΩ.
TERMINATION: RESISTANCE 20mΩ MAX AFTER ENVIRONMENTAL TESTING.
2 MECHANICAL:
CABLE TO PLUG TENSILE STRENGTH: 19.6N/PCS MIN.
DURABILITY: 200 MATING CYCLES.
3 MATERIAL & FINISH:
HOUSING: POLYCARBONATE, UL 94V-0 OR UL 94V-2.
COLOR: TRANSPARENT OR OTHER COLOR ARE AVAILABLE.
CONTACT BLADE: COPPER ALLOY.
CONDUCTOR: STRANDED & SOLID WIRE, 24AWG, 26 AWG.
GOLD PLATING: 50μ".
SHIELDED SHELL: COPPER ALLOY.



BLADE:	Z	ZL
Drawing		
Mark		

Quest Technology International, Inc. 11200 NW 138th St. Medley, FL 33178			
DIMENSION IN mm (Inch) TOLERANCE UNLESS OTHERWISE SPECIFIED	MATERIAL	图号 DWG NO.	PC NMP-8825
.X°±5°	名称 TITLE	SHIELDED MOD PLUG W/LOAD BAR, CAT6 RJ45, 8P8C,SOLID/STRD,50U,UL	
.XX±0.10	审核 APPROVAL	核对 CHECKED	制图 DRAWN
			Cathyli
		比例 SCALE	2/1
		角注 PROJ	
		张数 SHEET	1/1
		更改 REV	A