

# **Specification**

#### Description : Barracuda - 915MHz 8dBi Omni Antenna Outdoor Antenna

Features	:	Omni-Directional Radiation Pattern
		Collinear
		8dBi Peak Gain
		Robust Design for all Weather operation
		IP65 Waterproof
		Length: 1.474m
		Weight:870g
		Connector: N-type Female
		Wall/Pole Mount Bracket Included
		RoHS compliant





### **1.Introduction**

The OMB.915.B08F21 is a fiberglass omni-directional outdoor antenna, operating in 915 MHz ISM bad. The antenna has an 8dBi high peak gain, providing a large coverage area. Typical applications are in ISM, WLAN, RFID, SigFox, Lora and LPWA networks

The OMB.915.B08F21 Operated at 915MHz, with an 8dBi peak gain. The omnidirectional antenna collinear dipole design means it radiates uniformly in the azimuth with a high gain, providing coverage over long distances, thus minimizing the number of cells or nodes needed in a network.

The UV resistant fiberglass housing enables the OMB antenna to be utilized in all kinds of harsh environments, making it more robust and safer than traditional whip antennas. It has been designed to withstand high wind load. The integrated aluminum mounting bracket is perfect for directly mounting the antenna onto a pole or a wall.

The connector is industry standard N-type female. Connector can be customized subject to MOQ. Other frequencies and gains are available. Contact Taoglas reginal sales office for more details.



## 2. Specification

	ELECTRICAL		
Standard	ISM 868		
Band	902-928 MHz		
Antenna Type	Collinear Dipole Array		
Peak Gain	8 dBi		
Polarization	Vertical		
Impedance	50 ohms		
Max Input Power	50 watts		
VSWR	1.5:1		
Radiation	Omni-Directional		
Vertical Beam-width	14 Deg		
Horizontal Beam-width	360 Deg		
Antenna Design	Dipole Array		
Internal Material	Copper		
Connector	N Type Female		
	MECHANICAL		
Length	1475±5mm		
Bracket Dimension	70*73mm		
Antenna Weight	870g		
Radome Diameter	24mm		
Mounting Accessories	70g		
Application	Indoor/Outdoor		
Radome Material	White Fiberglass		
Base Material	Aluminum		
Mount Style	Pole Mount/Wall Mount		
Mounting	Stainless Steel		
Wind Resistance	>150mph(>241km/h)		
Waterproof	IP65		
	ENVIRONMENTAL		
Storage Temperature	-40°C to +80°C		
Operating Temperature	-40°C to +60°C		
Operating Humidity	10%~80% non-condensing		
Storage Humidity	5%~80% non-condensing		



### **3.Antenna Characteristics**

#### **3.1 Return Loss**



**3.2 VSWR** 





#### 3.3 Peak Gain





### 4.2D Radiation Pattern

Horizontal Pattern – H plane



Vertical Pattern – E plane





### 5. Mechanical Drawing (Unit: mm)



	Name	Material	Finish	QTY
1	OMB.915 Antenna	Fiberglass	White	1
2	Cover	ABS	Silver	1
3	Bracket	Aluminum	Silver	1
4	N Type(F) 1	Brass	Ni Plated	1
5	M6 U Bolt	Stainless Steel	Silver	1
6	M6 Washer 2	Stainless Steel	Silver	2
7	M6 Nut	Stainless Steel	Silver	2



### 6. Packaging



1 OMB.915.B0821 per tube Tube Dimensions - Ø80mm\*Height 1530mm Total Weight - 1280g



10 tubes per carton Carton Dimensions - 1550\*410\*190mm Weight - 14.48Kg



### **7.Antenna Installation Guide**





Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited. Copyright © Taoglas Ltd.