



WSMP

Male Full Detent to 2.92mm
Female Test Adapter

W1S102-K00S3



All dimensions are in inches [mm]

Unless otherwise specified, tolerances are as follows: .XXX ± .001 [0,025] .XXXX ± .0005 [0,012]

Interface

According to

Rosenberger WSMP™ Interface standards

Material and plating

Connector parts

WSMP (M) and 2.92mm Body

Material

Stainless Steel per
ASTM A582

Plating

Passivated

Contact

CuBe per ASTM B196

Hard gold 50µIN [1,27µm] min over
Nickel 50µIN [1,27µm] min

Dielectric
Dielectric

PTFE per D1710
Ultem® 1000 per ASTM D5205

Technical Data Sheet

Rosenberger

WSMP

Male Full Detent to 2.92mm
Female Test Adapter

W1S102-K00S3

Electrical data

Impedance	50 Ω
Frequency	DC to 40 GHz
Return loss (typical)	≥ 19 dB, DC to 40 GHz
Insertion loss	≤ 0.12 x √f(GHz) dB
Insulation resistance	≥ 3,500 MΩ
Center contact resistance	≤ 6.0 mΩ
Outer contact resistance	≤ 2.0 mΩ
Test voltage (at sea level)	250 V rms
RF High Potential (at sea level)	150 V rms @ 5 MHz
RF leakage	≥ -80 dB @ 3 GHz (typical mated pair)

Mechanical data

Mating cycles	
- Full Detent	≥ 100
- Smooth Bore	≥ 500
- Ultra Smooth Bore	≥ 500
Engagement force (typical)	
- Full Detent	2.5 lb _f [11 N]
- Smooth Bore	1.2 lb _f [5.3 N]
- Ultra Smooth Bore	1.0 lb _f [4.5 N]
Disengagement force (typical)	
- Smooth Bore	4.5 lb _f [20 N]
- Smooth Bore	1.0 lb _f [4.5 N]
- Ultra Smooth Bore	1.0 lb _f [4.5 N]

Environmental data

Temperature range	-55°C to +165°C
Thermal shock	MIL-STD-202-107, Condition B
Corrosion	MIL-STD-202-101
Vibration	MIL-STD-202-204, Condition D
Shock	MIL-STD-202-213, Condition I
Moisture resistance	MIL-STD-202-106, except Step 7B
Max soldering temperature	IEC 61760-1, +500°F [+260°C] for 10 seconds
2002/95/EC (RoHS)	compliant

Tooling

Extraction tool	N/A
-----------------	-----

Suitable cables

N/A

Packing

Standard

PROPRIETARY AND CONFIDENTIAL
 This data sheet is the property of Rosenberger of North America, LLC. By acceptance of this document you agree that all the rights to drawings, specifications, processes and other data therein, as well as the proprietary and novel features of the subject matter, are reserved by Rosenberger of North America, LLC and are disclosed in confidence. They are not to be manufactured, used, sold or disclosed to others, nor are devices embodying such features or information derived from these disclosures to be used or disclosed, unless and until expressly authorized by Rosenberger of North America, LLC. These drawings, specifications, processes, etc., are and remain the property of Rosenberger of North America, LLC, and are not to be copied or reproduced without permission.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
R. Hosler	8/18/14	M. Peeran	8/18/14	a00	Released per 19-s000	P. Sill	2/6/19
Rosenberger of North America, LLC P.O. Box 309 Akron, PA USA 17501 www.rosenbergerna.com				Tel. : +1.717.859.8900 Fax : +1.717.859.7044 Email : info@rosenbergerna.com			Page 2 / 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[W1S102-K00S3](#)