






备注

- 1.Copper,nickel base,matte tin
黄铜H62, 镍底, 镀雾锡
- 2.Wire screw hole M5
压线螺孔M5
- 3.Current Rating: 100A
额定电流: 100A
- 4.Operating temperature: -40℃ ~ +125℃
工作温度: -40℃ ~ +125℃
- 5.There shall be no defects such as
pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 6.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

HC - * * * * - ***** - D *** * - 02

Type	Screw Thread	Welding Feet	T=Anti Twist (防止扭动)	Series 0608×8.8mm 1620×16x20mm	D-DIP S-SMT FD=Flag Dip	Product No. 产品序号	Material 默认=Copper (黄铜) RC=Red Copper (紫铜)
M=Pull Teeth (抽牙)	3-M3 (螺牙)	(焊脚)					
RN=Rivet Nut (铆螺母)	4-M4 (螺牙)	2-2个					
	5-M5 (螺牙)	4-4个					
RG=Rivet Gasket (铆垫片)	6-M6 (螺牙)	6-6个					
		8-8个					

			GENERAL TOLERANCE	制 图 DRAWING	02					 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD		
			DIM TOL	审 核 CHECK								
			5 or more ±0.35	批 准 APPROVAL		产品名称 TITLE	PCB 焊接端子 插板 铆垫片 M5 6焊脚 14.5x14.5x12mm	版 本 REV.	A			
1	初版发行		2~5 ±0.25	比 例 SCALE		产品料号 PART NO.	HC-RG56-1414-D057-02	单 位 UNITS	mm			
			0~2 ±0.15	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1			
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle ±3.0°									



 深圳市华灿天禄电子有限公司
ShenzhenhuacantianluELECTRONICS CO., LTD