

Features

- Operation Voltage Range: 1.6V ~ 5.5V
- Low power current: $I_{CC}=10\mu A(\text{Max})$
- $\pm 24\text{mA}$ output drive ($V_{CC}=3.0\text{V}$)
- Power down protection
- SOT23-5 Package Available
- SOT353 Package Available
- SOT553 Package Available

General Description

The SN74LVC1G32 is a single 2-input OR gate which provides the Function $Y=A+B$ in positive logic circuit.

This device has power-down protective circuit to prevent the device from destruction when it is powered down.


Applications

- Voltage Level Shifting
- General Purpose Logic
- Power Down Signal Isolation
- Wide array of products such as:
 - PCs, Networking, Notebooks, Netbooks, PDAs
 - Tablet Computers, E-readers
 - Computer Peripherals, Hard Drives, CD/DVD ROM
 - TV, DVD, DVR, Set-Top Box
 - Cell Phones, Personal Navigation / GPS
 - MP3 Players, Cameras, Video Recorders


Ordering Information

ORDER NUMBER	PACKAGE DESCRIPTION	PACKAGE OPTION
SN74LVC1G32DBVR-TP	SOT23-5	Tape and Reel,3000
SN74LVC1G32DCKR-TP	SOT353	Tape and Reel,3000
SN74LVC1G32DRLR-TP	SOT553	Tape and Reel,4000

Logic Diagram



Pin Configuration



SOT23-5
SOT353
SOT553

Marking

SN74LVC1G32DBVR-TP Marking:C32F

SN74LVC1G32DCKR-TP Marking:CG5

SN74LVC1G32DRLR-TP Marking:CG7 Or CGR

Function Table

INPUT(A)	INPUT(B)	OUTPUT(Y)
H	X	H
X	H	H
L	L	L

Note: H: HIGH voltage level; L: LOW voltage level; X: Don't care.

Absolute Maximum Ratings

PARAMETER	SYMBOL	TEST CONDITIONS	RATINGS	UNIT
Supply Voltage	V_{CC}		-0.5 ~ +6.5	V
Input Voltage	V_{IN}		-0.5 ~ +6.5	V
Output Voltage	V_{OUT}	Output in the high or low state	-0.5 ~ $V_{CC}+0.5$	V
		Output in the high-impedance or power-off state	-0.5 ~ +6.5	V
V_{CC} or GND Current	I_{CC}		±100	mA
Continuous Output Current	I_{OUT}	$V_{OUT}=0 \sim V_{CC}$	±50	mA
Input Clamp Current	I_{IK}	$V_{IN}<0$	-50	mA
Output Clamp Current	I_{OK}	$V_{OUT}<0$	-50	mA
Operating Temperature	T_{OPR}		-40 ~ + 125	°C
Storage Temperature	T_{STG}		-65 ~ +150	°C

Note: Absolute maximum ratings are those values beyond which the device could be permanently damaged.
Absolute maximum ratings are stress ratings only and functional device operation is not implied.

Recommended Operating Conditions

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Supply Voltage	V_{CC}	Operating	1.65		5.5	V
		Data retention only	1.5			V
Input Voltage	V_{IN}		0		5.5	V
Output Voltage	V_{OUT}	High or low state	0		V_{CC}	V
Input Transition Rise or Fall Rate	$\Delta t/\Delta v$	$V_{CC}=1.8V\pm0.15V$			20	ns/V
		$V_{CC}=2.5V\pm0.2V$				
		$V_{CC}=3.3V\pm0.3V$			10	ns/V
		$V_{CC}=5V\pm0.5V$			5	ns/V
Operating Temperature	T_A		-40		+125	°C

Thermal Data

PARAMETER		SYMBOL	RATINGS	UNIT
Junction to Case	SOT-23-5	θ_{JC}	280	°C/W
	SOT-353		350	

Electrical Characteristics

PARAMETER	SYMBOL	TEST CONDITIONS	T _A =25°C			T _A =-40°C~+125°C			UNIT
			MIN	TYP	MAX	MIN	TYP	MAX	
High-Level Input Voltage	V _{IH}	V _{CC} =1.65V ~ 1.95V	0.65× V _{CC}			0.65× V _{CC}			V
		V _{CC} =2.3V ~ 2.7V	1.7			1.7			V
		V _{CC} =3V ~ 3.6V	2			2			V
		V _{CC} =4.5V ~ 5.5V	0.7×V _{CC}			0.7×V _{CC}			V
Low-Level Input Voltage	V _{IL}	V _{CC} =1.65V ~ 1.95V			0.35× V _{CC}			0.35× V _{CC}	V
		V _{CC} =2.3V ~ 2.7V			0.7			0.7	V
		V _{CC} =3V ~ 3.6V			0.8			0.8	V
		V _{CC} =4.5V ~ 5.5V			0.3×V _{CC}			0.3×V _{CC}	V
High-Level Output Voltage	V _{OH}	V _{CC} =1.65 ~ 5.5V, I _{OH} =-100μA	V _{CC} -0.1			V _{CC} -0.1			V
		V _{CC} =1.65V, I _{OH} =-4mA	1.2			0.95			V
		V _{CC} =2.3V, I _{OH} =-8mA	1.9			1.7			V
		V _{CC} =3.0V, I _{OH} =-16mA	2.4			2.1			V
		V _{CC} =3.0V, I _{OH} =-24mA	2.3			2.0			V
Low-Level Output Voltage	V _{OL}	V _{CC} =4.5V, I _{OH} =-32mA	3.8			3.4			V
		V _{CC} =1.65 ~ 5.5V, I _{OL} =100μA			0.1			0.1	V
		V _{CC} =1.65V, I _{OL} =4mA			0.45			0.7	V
		V _{CC} =2.3V, I _{OL} =8mA			0.3			0.45	V
		V _{CC} =3.0V, I _{OL} =16mA			0.4			0.5	V
Input Leakage Current	I _{I(LEAK)}	V _{CC} =0 ~ 5.5V, V _{IN} =5.5V or GND			±5			±5	μA
Power OFF Leakage Current	I _{OFF}	V _{CC} =0V, V _{IN} or V _{OUT} =5.5V			±10			±25	μA
Quiescent Supply Current	I _Q	V _{CC} =1.65 ~ 5.5V, V _{IN} =5.5V or GND, I _{OUT} =0			10			10	μA
Additional Quiescent Supply Current Per Input Pin	ΔI _Q	V _{CC} =3 ~ 5.5V, One input at V _{CC} -0.6V, Other inputs at V _{CC} or GND			500			500	μA


Dynamic Characteristics (Input: t_R, t_F≤3ns; P_{RR}≤1MHz)

PARAMETER	SYMBOL	TEST CONDITIONS	T _A =25°C			T _A =-40°C~+125°C			UNIT
			MIN	TYP	MAX	MIN	TYP	MAX	
Propagation Delay From Input (A) to Output (Y)	t _{PLH} / t _{PHL}	C _L =15pF, R _L =1MΩ	V _{CC} =1.8±0.15V	1.9		9		12	ns
			V _{CC} =2.5±0.2V	0.8		6.5		9	ns
			V _{CC} =3.3±0.3V	0.9		5.5		8	ns
			V _{CC} =5±0.5V	0.8		5		7	ns
		C _L =30pF, R _L =1KΩ	V _{CC} =1.8±0.15V	2.8		9.5		12.5	ns
			V _{CC} =2.5±0.2V	1.2		7.5		10	ns
			V _{CC} =3.3±0.3V	1.1		6.5		9	ns
			V _{CC} =5±0.5V	1		6		8	ns

Operating Characteristics


PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Input Capacitance	C_{IN}	$V_{CC}=3.3V$, $V_{IN}=V_{CC}$ or GND		4		pF
Power Dissipation Capacitance	C_{PD}	$V_{CC}=1.8V$		20		pF
		$V_{CC}=2.5V$		20		pF
		$V_{CC}=3.3V$		21		pF
		$V_{CC}=5V$		22		pF

Test Circuit And Waveforms



TEST CIRCUIT


V_{CC}	INPUTS		V_M	C_L	R_L
	V_{IN}	t_R, t_F			
$1.8V \pm 0.15V$	V_{CC}	$\leq 2ns$	$V_{CC}/2$	15pF	1M Ω
$2.5V \pm 0.2V$	V_{CC}	$\leq 2ns$	$V_{CC}/2$	15pF	1M Ω
$3.3V \pm 0.3V$	3V	$\leq 2.5ns$	1.5V	15pF	1M Ω
$5V \pm 0.5V$	V_{CC}	$\leq 2.5ns$	$V_{CC}/2$	15pF	1M Ω
$1.8V \pm 0.15V$	V_{CC}	$\leq 2ns$	$V_{CC}/2$	30pF	1K Ω
$2.5V \pm 0.2V$	V_{CC}	$\leq 2ns$	$V_{CC}/2$	30pF	500 Ω
$3.3V \pm 0.3V$	3V	$\leq 2.5ns$	1.5V	50pF	500 Ω
$5V \pm 0.5V$	V_{CC}	$\leq 2.5ns$	$V_{CC}/2$	50pF	500 Ω



PROPAGATION DELAY TIMES


Package Outline Dimensions (Unit: mm)

SOT23-5




Dimension	Min.	Max.
A	2.80	3.00
B	1.50	1.70
C	1.00	1.20
D	0.35	0.45
E	0.35	0.55
F	1.80	2.00
G	0.90	1.00
H	0.02	0.10
J	0.10	0.20
K	2.60	3.00

Mounting Pad Layout (Unit: mm)




Package Outline Dimensions (Unit: mm)

SOT353



Dimension	Min.	Max.
A	2.00	2.20
B	1.15	1.35
C	0.85	1.05
D	0.15	0.35
E	0.25	0.40
F	1.20	1.40
G	0.60	0.70
H	0.02	0.10
J	0.05	0.15
K	2.20	2.40

Mounting Pad Layout (Unit: mm)





TECH PUBLIC

—台丹电子—


SN74LVC1G32

SINGLE 2-INPUT EXCLUSIVE-OR GATE

www.sot23.com.tw

Package Outline Dimensions (Unit: mm)

SOT553



Dimension	Min.	Max.
A	1.500	1.700
B	1.100	1.300
C	0.525	0.600
D	0.170	0.270
E	0.100	0.300
F	0.400	0.600
G	0.450	0.550
H	0.000	0.050
J	0.090	0.160
K	1.500	1.700

Mounting Pad Layout (Unit: mm)

