

## Sales Outline Drawing

Revision:

D

## cUL Recognized to IEC60601-1-8 AMD1

## Oxygen Melody

## Specifications:


Sound Level Category:	Silent	Loud	Loud	Loud
Mode of Operation:	Silent	Continuous	Medium Priority Alarm - 3 beeps repeating every 7.5 sec	Medium Pulse @ 5PPS
Loudness @ 10cm:	Silent	85 to 95 dB(A) Typ.	85 to 95 dB(A) Typ.	85 to 95 dB(A) Typ.
Frequency:	Silent	2500 ± 300Hz	150 to 4000 Hz	2500 ± 300Hz
Connection:	Connect "+" to "+" & " - " to " - " of Power Supply	Connect "+" to "+" & " - " & Low to " - " of Power Supply	Connect "+" to "+" & " - " & Medium to " - " of Power Supply	Connect "+" to "+" & " - " & High to " - " of Power Supply
Average Current Draw:	<20mA Typ.	<225mA Typ.	<70mA Typ.	<225mA Typ.
Voltage Rating:		5 ± 0.5 VDC		
Ipk Current*:		400mA		
Housing Material:		Valox (UL94V-0), Octagonal, Black		
Storage Temperature:		-30° to +60° C		
Operating Temperature:		-30° to +55° C		
Weight Typical:		6.0g		
Options:		Please contact factory.		

## Dimensions: Inches [mm]

## cUL Recognized

## ROHS Compliant

PATENT NUMBER: 7880593



NOTE A:

TERMINALS - .031" DIA. NICKEL/TIN COATED BRASS.

NOTE B:

MOUNTING- INSERT INTO PRINTED CIRCUIT BOARD AND HAND OR MACHINE SOLDER.  
UNITS ARE SUITABLE FOR WAVE SOLDERING. BOARDS ARE NOT SUITABLE FOR WASH.  
RECOMMENDED MAXIMUM TEMPERATURE AND TIME DURATION FOR WAVE SOLDERING IS  
+270°C AND 3 SECONDS RESPECTIVELY.

\*Ipk = Instantaneous Peak