




REV. 0
DCO 16895


COIL: @ 25°C
RESISTANCE 75 OHMS ± 10%
NOMINAL VOLTAGE 6.0 VDC
MUST OPERATE 2.75 VDC
MUST RELEASE 1.65 VDC MAX, 0.27 VDC MIN

ENVIRONMENT:

VIBRATION 10 CPS TO 2500 CPS @ 20 g's
SHOCK 50 g's 11 MS. DURATION
TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 6 MS MAX
RELEASE 5 MS MAX
CONTACT STABILIZATION 2.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: 2 AMPS 28 VDC
0.1 AMP 115 VAC RESISTIVE 0.5 AMPS
28 VDC INDUCTIVE 100,000 OPERATIONS

DR. PBB 3/23/01 CK. TLG 03-23-01

IC Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M39016/44-017M REV. "HMS" RELAY

HMS1201S109M