



Pushing Performance  
Since 1945

# D SUB MIXED FE HV\_CRIMP\_S4




Image is for illustration purposes only. Please refer to product description.

Part number	09 69 182 2550
Specification	D SUB MIXED FE HV_CRIMP_S4
HARTING eCatalogue	<a href="https://b2b.harting.com/09691822550">https://b2b.harting.com/09691822550</a>

## Identification

Category	Contacts
Series	D-Sub
Identification	Mixed
Type of contact	Crimp contact
Description of the contact	Straight

## Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts

## Technical characteristics

Conductor cross-section	0.05 ... 0.25 mm²
Conductor cross-section [AWG]	AWG 30 ... AWG 24
Rated current	≤10 A
Rated voltage	≤3,000 V >1,000 V
Contact resistance	≤3 mΩ
Stripping length	1.5 mm
Limiting temperature	-55 ... +125 °C
Insertion force	≤5 N
Withdrawal force	≈2.5 N
Performance level	AU 50 1



**Pushing Performance**  
Since 1945

## Technical characteristics

Mating cycles	≥500
Test voltage $U_{r.m.s.}$	4 kV @ 50 Hz

## Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni
Layer thickness	≥1.27 µm
Layer thickness	≥50 µinch
Material (hood/housing)	Polycarbonate / Teflon (PTFE)
Material (locking)	PI
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Commercial data

Packaging size	20
Net weight	0.899 g
Country of origin	Czechia
European customs tariff number	85366990
GTIN	5713140096943
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors