

<b>SIDAC</b> <b>SILICON UNIDIRECTIONAL THYRISTORS</b>	<b>1 AMPERE</b> <b>220 VOLTS</b>
--	-------------------------------------

#### FEATURES

- $V_{BO}$  range is from 210 to 230 Vdc
- $V_{DRM}$  with stand 190V
- $I_H$  is under 60 mA
- Compact package for spacing saving.


#### Application

- Gas Igniters

#### MECHANICAL DATA

- Case: JEDEC DO-15 molded plastic
- Terminals: Lead Free Plating
- Component in accordance to RoHs 2011/65/EU
- UL Recognition File # E219635

#### DO-15



DO-15		
Dim.	Min.	Max.
A	25.4	-
B	5.80	7.60
C	0.71 $\varnothing$	0.86 $\varnothing$
D	2.60 $\varnothing$	3.60 $\varnothing$
All Dimensions in millimeter		



#### MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

##### ABSOLUTE RATING

PARAMETER	TEST CONDITION		SYMBOL	VALUE	UNIT
Peak repetitive off-state voltage	TJ= -40 to 125°C, sine wave, 50 to 60 Hz		V <sub>DRM</sub>	190	V
On-state RMS current	TL= 80°C, all conduction angles		IT(RMS)	1	A
Pulse on-state current	Ta=25°C, pulse width to = 10us, sine wave, repetitive peak value	f=5Hz	ITRM	330	A
		f=60Hz		190	
Maximum lead solder temperature (Lead length ≥ 1/16 " from case, 10s max)			TL	260	°C
Operating junction temperature range			TJ	-40 ~ +125	°C
Storage temperature range			TSTG	-40 ~ +150	°C

##### THERMAL PERFORMANCE

PARAMETER	SYMBOL	TYP.	UNIT
Typical thermal resistance junction to case	$R_{thJC}$	15	$^\circ\text{C/W}$

##### OFF CHARACTERISTICS

PARAMETER	SYMBOL	MAX	UNIT
Peak repetitive forward or reverse blocking current (50 to 60 Hz) $V_{DRM}=190\text{V}$	$I_{DRM}$	10	$\mu\text{A}$

##### ON CHARACTERISTICS

PARAMETER	TEST CONDITION	SYMBOL	MIN	TYP.	MAX	UNIT
Peak on-state voltage	$I_T = 1 \text{ A}$	$V_{TM}$	--	1.1	1.5	V
Breakover voltage	$I_{BO} = 5 \mu\text{A}$	$V_{BO}$	210	220	230	V
Breakover current		$I_{BO}$	--	--	200	$\mu\text{A}$
Holding current		$I_H$	--	--	60	mA
Switching resistance		$R_s$	0.1	--	--	$k\Omega$

##### ON CHARACTERISTICS


PARAMETER	SYMBOL	MIN	TYP.	MAX	UNIT
Critical rate of rise of on-state current	$di/dt$	--	220	--	A/ $\mu\text{S}$

#### Note :


Maximum ratings are those values beyond which device damage can occur.  
Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously.  
If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.

REV-1, JUN.-2017, KDxD07


**Fig.1- TYPICAL ON-STATE VOLTAGE**




**Fig.2- TYPICAL POWER DISSIPATION**



**Fig.3- TYPICAL BREAKOVER VOLTAGE**



**Fig.4- TYPICAL HOLDING CURRENT**



### **Important Notice and Disclaimer**

LSC reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

LSC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does LSC assume any liability for application assistance or customer product design. LSC does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of LSC.

LSC products are not authorized for use as critical components in life support devices or systems without express written approval of LSC.