


# MCV 0,5/10-G-2,5 THT R44 - PCB header



1963845

<https://www.phoenixcontact.com/us/products/1963845>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB headers, nominal cross section: 0.5 mm<sup>2</sup>, color: black, nominal current: 4 A, rated voltage (III/2): 160 V, contact surface: Sn, contact connection type: Pin, number of potentials: 10, number of rows: 1, number of positions: 10, number of connections: 10, product range: MCV 0,5/..-G-THT, pitch: 2.5 mm, mounting: THR soldering / wave soldering, pin layout: Linear pinning, solder pin [P]: 3.5 mm, number of solder pins per potential: 1, plug-in system: COMBICON FK-MC 0,5, Pin connector pattern alignment: Standard, locking: without, mounting: without, type of packaging: 44 mm wide tape, User information and design recommendations on Through Hole Reflow Technology can be found at: "Downloads"

## Your advantages

- Designed for integration into the SMT soldering process
- Vertical connection enables multi-row arrangement on the PCB

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1963845                        |
| Packing unit                         | 220 pc                         |
| Minimum order quantity               | 220 pc                         |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AA01                           |
| Product key                          | AAATGB                         |
| Catalog page                         | Page 171 (C-1-2013)            |
| GTIN                                 | 4017918916459                  |
| Weight per piece (including packing) | 5.02 g                         |
| Weight per piece (excluding packing) | 3.967 g                        |
| Customs tariff number                | 85366930                       |
| Country of origin                    | DE                             |

# MCV 0,5/10-G-2,5 THT R44 - PCB header



1963845

<https://www.phoenixcontact.com/us/products/1963845>

## Technical data

### Product properties

|                           |                                            |
|---------------------------|--------------------------------------------|
| Product type              | PCB headers                                |
| Product family            | MCV 0,5/..-G-THT                           |
| Product line              | COMBICON Connectors XS                     |
| Type                      | Component suitable for through hole reflow |
| Number of positions       | 10                                         |
| Pitch                     | 2.5 mm                                     |
| Number of connections     | 10                                         |
| Number of rows            | 1                                          |
| Number of potentials      | 10                                         |
| Mounting flange           | without                                    |
| Pin layout                | Linear pinning                             |
| Solder pins per potential | 1                                          |

### Data management status

|                  |    |
|------------------|----|
| Article revision | 02 |
|------------------|----|

### Electrical properties

|                             |        |
|-----------------------------|--------|
| Nominal current $I_N$       | 4 A    |
| Nominal voltage $U_N$       | 160 V  |
| Contact resistance          | 2 mΩ   |
| Rated voltage (III/3)       | 32 V   |
| Rated surge voltage (III/3) | 1.5 kV |
| Rated voltage (III/2)       | 160 V  |
| Rated surge voltage (III/2) | 2.5 kV |
| Rated voltage (II/2)        | 160 V  |
| Rated surge voltage (II/2)  | 2.5 kV |

### Mounting

|               |                                |
|---------------|--------------------------------|
| Mounting type | THR soldering / wave soldering |
| Pin layout    | Linear pinning                 |

### Processing notes

|                                  |                       |
|----------------------------------|-----------------------|
| Process                          | Reflow/wave soldering |
| Moisture Sensitive Level         | MSL 3                 |
| Classification temperature $T_c$ | 245 °C                |
| Solder cycles in the reflow      | 3                     |

### Material specifications

#### Material data - contact

|      |                                                                                  |
|------|----------------------------------------------------------------------------------|
| Note | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
|------|----------------------------------------------------------------------------------|

# MCV 0,5/10-G-2,5 THT R44 - PCB header



1963845


<https://www.phoenixcontact.com/us/products/1963845>

|                                             |                      |
|---------------------------------------------|----------------------|
| Contact material                            | Cu alloy             |
| Surface characteristics                     | Tin-plated           |
| Metal surface contact area (top layer)      | Tin (3 - 5 µm Sn)    |
| Metal surface contact area (middle layer)   | Nickel (1 - 3 µm Ni) |
| Metal surface soldering area (top layer)    | Tin (3 - 5 µm Sn)    |
| Metal surface soldering area (middle layer) | Nickel (1 - 3 µm Ni) |

## Material data - housing

|                                                                   |              |
|-------------------------------------------------------------------|--------------|
| Color (Housing)                                                   | black (9005) |
| Insulating material                                               | PA           |
| Insulating material group                                         | IIIa         |
| CTI according to IEC 60112                                        | 250          |
| Flammability rating according to UL 94                            | V0           |
| Glow wire flammability index GWFI according to EN 60695-2-12      | 850          |
| Glow wire ignition temperature GWIT according to EN 60695-2-13    | 775          |
| Temperature for the ball pressure test according to EN 60695-10-2 | 125 °C       |

## Dimensions

|                       |                                                                                      |
|-----------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing   |  |
| Pitch                 | 2.5 mm                                                                               |
| Width [w]             | 26.9 mm                                                                              |
| Height [h]            | 13.6 mm                                                                              |
| Length [l]            | 8.1 mm                                                                               |
| Installed height      | 10.1 mm                                                                              |
| Solder pin length [P] | 3.5 mm                                                                               |
| Pin dimensions        | 0.8 x 0.8 mm                                                                         |

## PCB design

|               |         |
|---------------|---------|
| Pin spacing   | 2.50 mm |
| Hole diameter | 1.4 mm  |

## Mechanical tests

### Visual inspection

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-1:2002-02 |
| Result        | Test passed           |

### Dimension check

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-2:2002-02 |
| Result        | Test passed           |

# MCV 0,5/10-G-2,5 THT R44 - PCB header



1963845

<https://www.phoenixcontact.com/us/products/1963845>

## Resistance of inscriptions

|               |                        |
|---------------|------------------------|
| Specification | IEC 60068-2-70:1995-12 |
| Result        | Test passed            |

## Polarization and coding

|               |                        |
|---------------|------------------------|
| Specification | IEC 60512-13-5:2006-02 |
| Result        | Test passed            |

## Contact holder in insert

|                                                |                        |
|------------------------------------------------|------------------------|
| Specification                                  | IEC 60512-15-1:2008-05 |
| Contact holder in insert<br>Requirements >20 N | Test passed            |

## Insertion and withdrawal forces

|                                     |             |
|-------------------------------------|-------------|
| Result                              | Test passed |
| No. of cycles                       | 25          |
| Insertion strength per pos. approx. | 8 N         |
| Withdraw strength per pos. approx.  | 6 N         |

## Electrical tests

### Thermal test | Test group C

|                            |                       |
|----------------------------|-----------------------|
| Specification              | IEC 60512-5-1:2002-02 |
| Tested number of positions | 12                    |

### Insulation resistance

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-3-1:2002-02 |
| Insulation resistance, neighboring positions | $10^{12} \Omega$      |

### Air clearances and creepage distances |

|                                                        |                     |
|--------------------------------------------------------|---------------------|
| Specification                                          | IEC 60664-1:2007-04 |
| Insulating material group                              | IIIa                |
| Comparative tracking index (IEC 60112)                 | CTI 250             |
| Rated insulation voltage (III/3)                       | 32 V                |
| Rated surge voltage (III/3)                            | 1.5 kV              |
| minimum clearance value - non-homogenous field (III/3) | 0.8 mm              |
| minimum creepage distance (III/3)                      | 1.3 mm              |
| Rated insulation voltage (III/2)                       | 160 V               |
| Rated surge voltage (III/2)                            | 2.5 kV              |
| minimum clearance value - non-homogenous field (III/2) | 1.5 mm              |
| minimum creepage distance (III/2)                      | 1.6 mm              |
| Rated insulation voltage (II/2)                        | 160 V               |
| Rated surge voltage (II/2)                             | 2.5 kV              |
| minimum clearance value - non-homogenous field (II/2)  | 0.5 mm              |
| minimum creepage distance (II/2)                       | 1.6 mm              |

## Environmental and real-life conditions

# MCV 0,5/10-G-2,5 THT R44 - PCB header



1963845

<https://www.phoenixcontact.com/us/products/1963845>

## Vibration test

|                        |                             |
|------------------------|-----------------------------|
| Specification          | IEC 60068-2-6:2007-12       |
| Frequency              | 10 - 150 - 10 Hz            |
| Sweep speed            | 1 octave/min                |
| Amplitude              | 0.35 mm (10 Hz ... 60.1 Hz) |
| Acceleration           | 5g (60.1 Hz ... 150 Hz)     |
| Test duration per axis | 2.5 h                       |
| Test directions        | X-, Y- and Z-axis           |

## Durability test

|                                        |                       |
|----------------------------------------|-----------------------|
| Specification                          | IEC 60512-9-1:2010-03 |
| Impulse withstand voltage at sea level | 2.95 kV               |
| Contact resistance $R_1$               | 2 m $\Omega$          |
| Contact resistance $R_2$               | 2.2 m $\Omega$        |
| Insertion/withdrawal cycles            | 25                    |


## Climatic test

|                                   |                                                                           |
|-----------------------------------|---------------------------------------------------------------------------|
| Specification                     | ISO 6988:1985-02                                                          |
| Corrosive stress                  | 0.2 dm <sup>3</sup> SO <sub>2</sub> on 300 dm <sup>3</sup> /40 °C/1 cycle |
| Thermal stress                    | 100 °C/168 h                                                              |
| Power-frequency withstand voltage | 1.39 kV                                                                   |

## Ambient conditions


|                                         |                                                     |
|-----------------------------------------|-----------------------------------------------------|
| Ambient temperature (operation)         | -40 °C ... 100 °C (dependent on the derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                    |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                       |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                    |

## Packaging specifications


|                             |                                                                                      |
|-----------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing         |  |
| Type of packaging           | 44 mm wide tape                                                                      |
| [W] tape width              | 44 mm                                                                                |
| [W2] coil overall dimension | 50.4 mm                                                                              |
| [A] coil diameter           | 330 mm                                                                               |
| Outer packaging type        | Dry bag                                                                              |
| ESD level                   | (D) electrostatically conductive                                                     |
| Specification               | DIN EN 61340-5-1 (VDE 0300-5-1): 2008-07                                             |

## Drawings

Drilling plan/solder pad geometry



Dimensional drawing




# MCV 0,5/10-G-2,5 THT R44 - PCB header

1963845


<https://www.phoenixcontact.com/us/products/1963845>



Dimensional drawing



Diagram



Type: FK-MC 0,5/...-ST-2,5 with MCV 0,5/...-G-2,5 THT


# MCV 0,5/10-G-2,5 THT R44 - PCB header

1963845

<https://www.phoenixcontact.com/us/products/1963845>



Dimensional drawing



# MCV 0,5/10-G-2,5 THT R44 - PCB header



1963845

<https://www.phoenixcontact.com/us/products/1963845>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1963845>

|                                                                                                                                                       |                       |                       |                   |                             |
|-------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
| <div> <b>cULus Recognized</b><br/>Approval ID: E60425-19990913</div> |                       |                       |                   |                             |
|                                                                                                                                                       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| Use group B                                                                                                                                           |                       |                       |                   |                             |
|                                                                                                                                                       | 125 V                 | 4 A                   | -                 | -                           |

|                                                                                                                                                                       |                       |                       |                   |                             |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
| <div> <b>VDE Gutachten mit Fertigungsüberwachung</b><br/>Approval ID: 40013394</div> |                       |                       |                   |                             |
|                                                                                                                                                                       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                                                                                                                                       | 32 V                  | 4 A                   | -                 | -                           |

# MCV 0,5/10-G-2,5 THT R44 - PCB header



1963845

<https://www.phoenixcontact.com/us/products/1963845>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27460201 |
| ECLASS-12.0 | 27460201 |
| ECLASS-13.0 | 27460201 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002637 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# MCV 0,5/10-G-2,5 THT R44 - PCB header



1963845

<https://www.phoenixcontact.com/us/products/1963845>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)