

## Pushbutton Ø 22 mm silver contact

82-6571.2000



<https://eao.com/p/82-6571.2000>

Your product:

---



82-6571.2000  
Pushbutton Ø 22 mm silver contact

#### FRONT

Front form:	round
Front dimension:	Ø 25 mm
Front bezel material:	Aluminium
Front bezel shape:	flush

#### MOUNTING

Mounting type:	Panel mounting
Mounting cut-out:	Ø 22 mm

#### OPERATING-/INDICATION PART

Lens optics:	opaque
Lens illumination:	non illuminative
Lens shape:	convex
Lens material:	Aluminium
Lens colour:	Nature

#### ELECTRICAL CHARACTERISTICS

Pollution degree:	2, according to EN IEC 60947-1
Rated insulation voltage Ui:	250 V
Electric strength:	1500 VAC, 50 Hz 1 minute between live terminals and ground
Switching voltage and switching current:	

according to IEC 60947-5-1 (Silver contacts)

Service categorie AC-15

Voltage	Current
24 VAC	1 A
35 VAC	1 A (M12 version)
110 VAC	1 A
220 VAC	0.5 A

Switch rating DC service categorie DC-13 (Silver contacts)

Voltage	Current
24 VDC	0.7 A
35 VDC	0.5 A (M12 version)
110 VDC	0.2 A
220 VDC	0.1 A

according to UL 508 (Silver contacts)

$\cos\phi$  0,75 ... 0,8

Voltage	Current
120 VAC	5 A
240 VAC	3 A
24 VAC	1 A

**Electrical lifetime:** 50 000 cycles of operation

**Thermal current  $I_{th}$ :** 5 A

**Contacts:** 1 C

**Rated Operational Voltage  $U_e$ :** 250 VAC

## MECHANICAL CHARACTERISTIC

**Switching action:** Maintained

**Terminal:** Soldering terminal, 2.8 x 0.5 mm

**Operating Travel:** ca. 3 mm

**Contact material:** Silver

**Operating force:** 4 N ... 7 N

**Switching system:** Snap-action switching element

**Tightening torque:** 0.5 ... 0.6 Nm

**Mechanical lifetime:** 500 000 cycles of operation

**Weight:** 0.019 kg

## AMBIENT CONDITION

**Climate resistance:** Damp heat, 21 days according to IEC 60512-11

**Operating temperature:** - 30 °C ... + 70 °C

**Vibration resistance:** 10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6

**Shock resistance:** Max. 500 m / s<sup>2</sup> as per IEC 60068-2-27

**Storage temperature:**

– 40 °C ... + 80 °C

**IP front protection:**

IP65, IP67

## CERTIFICATE

**Conformities:**

CE, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)

**Approbations:**

CB, CCC, C UL, UL

**REACH:**

REACH compliant

**RoHS:**


RoHS compliant

## OTHER


**Short Description:**

Pushbutton Ø 22 mm silver contact, Maintained, 1 C, Soldering terminal, 2.8 x 0.5 mm, round, Aluminium, Nature

**Mounting cut-outs:**




**Dimension drawings:**



A = Solder terminal  
B = Screw terminal

**Wiring diagrams:**



**Component layouts:**

