

# COAXIAL SURGE PROTECTOR DEVICE, GDT technology up to 2.5 GHz

3402.17.0044

## Properties

- Broadband frequency operation from DC to 2.5 GHz
- Gas discharge tube replaceable and not included
- DC/AC remote powering via coaxial same cable
- Surge current handling capability 30 kA once and 20 kA multiple
- Semper self-extinguishing functionality optional



CE UK  
CA

## Product configuration

Main path connectors	Port 1: unprotected, N jack (female) Port 2: protected, N jack (female)
Mounting and grounding	MH12 (bulkhead mounting), M8 (screw)
Side of bulkhead	protected side
EMP can be install reversed	YES

## Interface and material data

Housing material / plating	Brass / SUCOPLATE (R) Plating
Center contact, material / plating	Port 1: Copper Beryllium Alloy / Gold Plating (without Nickel underplating) Port 2: Copper Beryllium Alloy / Gold Plating (without Nickel underplating)

## Electrical data

Impedance	50 Ω
Frequency frame	0 MHz to 2500 MHz
Return loss typical	≥ 20 dB
Insertion loss typical	≤ 0.2 dB
CW power frame	≤ 150 W
Residual pulse energy (typ.)	350 μJ (test pulse 4 kV 1.2/50 μs; 2 kA 8/20 μs)
Residual pulse voltage (typ.)	650 V (test pulse 4 kV 1.2/50 μs; 2 kA 8/20 μs)
Surge current handling capability	30 kA single, 20 kA multiple (test pulse 8/20 μs)

**COAXIAL SURGE PROTECTOR DEVICE, GDT technology up to 2.5 GHz**

3402.17.0044

**Electrical remarks**

Gas tube	Yes DC, GDT not included
Electrical remarks	Data refer to GDT 9071.99.0547, 230 V

**Mechanical data**

Weight	230 g
Mating cycles	500

**Environmental data**

Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	IP65
Thermal shock according	MIL-STD-202, Method 107, Cond. B
Vibration according	MIL-STD-202, Method 204, Cond. D
Moisture resistance according	MIL-STD-202, Method 106

**Ordering Information Table**

Item number	Item description
23001424	3402.17.0044

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.  
DOCUMENT PIM-P2015 / Date of publication: 31.10.2024 / uncontrolled copy