


PRODUCT NUMBER: 3128-2-00-15-00-00-08-0

3128-X-00-XX-00-00-08-0 Soldermount in .024 min. mounting hole 	<table border="1"> <thead> <tr> <th>Basic Part Number</th><th>Length A</th></tr> </thead> <tbody> <tr> <td>3128-1</td><td>.250</td></tr> <tr> <td>3128-2</td><td>.425</td></tr> <tr> <td>3128-3</td><td>.525</td></tr> <tr> <td>3128-4</td><td>.550</td></tr> <tr> <td>3128-5</td><td>.930</td></tr> </tbody> </table>	Basic Part Number	Length A	3128-1	.250	3128-2	.425	3128-3	.525	3128-4	.550	3128-5	.930
Basic Part Number	Length A												
3128-1	.250												
3128-2	.425												
3128-3	.525												
3128-4	.550												
3128-5	.930												

DESCRIPTION

Solder Mount PCB Pin

Current Rating:

Application Specific mA

Operating Temperature Range:

-55/+125° C mA

Mounting Feature:

Through-Hole Solder Mount

Tail Type: Solder tail

Mounting Hole: .024" (0,610mm)

Tail Diameter: .020" (0,508mm)

Packaging: 00 - Packaged in Bulk

Shell Plating	Contact Plating	ROHS
---------------	-----------------	------

10 μ " Gold over Nickel

No Plating on Inner Contact



STANDARD TOLERANCES ON PCB TERMINAL PINS & RECEPTACLES

Diameters $+\text{-}.002"$

Lengths $+\text{-}.005"$

Angles $+\text{-} 2^\circ$

STANDARD TOLERANCES ON SPRING-LOADED PINS

Diameters $+\text{-}.002"$

Lengths $+\text{-}.006"$

Angles $+\text{-} 2^\circ$

ADDITIONAL NOTES & SPECIFICATIONS

In the interest of improved design, quality and performance, Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.