

SENCITY® Rail Antenna

727313

Properties

- Supports the frequency range of 87.5 - 108 MHz as a receive-only antenna
- Rugged design, meets EN 50155 Railway Standard
- Fire retardant acc. to EN 45545-2
- Contains a heavy duty fibreglass radome



Electrical bands	
	Band 1
Name	4M band
Frequency	87.5 MHz ... 108 MHz
Impedance	50 Ω
Ambient Temperature	25 °C

Ports	
	Port 1
Port name	4M band
Connector	N, jack (female)
Polarization	vertical
DC grounded	Yes

Connections	
Port number	Port 1
Band 1	✓

Mechanical data	
Weight	0.9 kg
Dimensions	355 mm x 145 mm x 80 mm (Height x Width x Depth)
Remarks	Flange: Aluminum. Radiator: Copper. All screws and nuts: Stainless steel. Sealing: Neoprene and EPDM. Packaging size (outside): 151 x 90 x 415 mm


SENCITY® Rail Antenna
727313

Interface and material data	
Radome material	Fiberglass
Radome colour	Grey
Back plate/base plate material	Aluminium
Back plate/base plate colour	Grey

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Environment (application)	Outdoor
Ingress protection (IP Rating)	Mated / IP66
Flammability rating	EN 45545-2

Environmental remarks	
Environmental tests: EN 50155:2018-05	

Outline drawing



HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.

SENCITY® Rail Antenna

727313

DOCUMENT PIM-P35343 / Date of publication: 06.06.2024 / uncontrolled copy