






PRODUCT NO	DIM L	DIM M	PLATING	RECOMMENDED P.C BOARD THICKNESS
10125340-003LF	2.70	2.10	NOTE 2	1.57mm (0.062") / 2.36mm(0.093")



NOTE:
ALL OTHER DIMENSIONS, REFER TO SHEET 1 & 2.

spec ref -				dr	Guat-Lian Loo	2013/05/10	projection 	MM 	size	A3	scale	3:1
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Guat-Lian Loo	2016/03/03			ecn no	ELX-S-23205-1		
				chr	-	-			rel level			Released
				appr	Koon-Poh Tay	2016/03/04	product family			SAS		
surface ISO 1302	linear	0.X	± -	Amphenol FCi	title 12G SAS RECEPTACLE VERTICAL PF TYPE ASSY			dwg no	10125340			rev B
		0.XX	±0.20									
		0.XXX	± -									
	angular	0°	±2°		cat. no.		-	Product - Customer Drw			sheet 3 of 5	

