

COAXIAL CONNECTOR, SMA, 50 Ohm, Straight cable plug (male)

11_SMA-50-4-102/199_N

Properties

- Excellent corrosion resistance in a wide range of environments
- High salt mist resistant
- Material 316L stainless steel
- Excellent return loss values
- Applicable in frequencies up to 18 GHz

**Product configuration**

Interface type	Gender	Standard
SMA	plug	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Interface and material data

Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Stainless Steel (high salt mist resistant)	Passivated (Plating)
Body	Stainless Steel (high salt mist resistant)	Passivated (Plating)
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Stainless Steel (high salt mist resistant)	Passivated (Plating)
Gasket	VMQ (Silicone rubber)	

Electrical data

Impedance	50 Ω
Interface frequency	18 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0.1 GHz ... 2 GHz	28 dB	1.08
2 GHz ... 4 GHz	26 dB	1.11
4 GHz ... 8 GHz	23 dB	1.15

Mechanical data

Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	crimped

COAXIAL CONNECTOR, SMA, 50 Ohm, Straight cable plug (male)
11_SMA-50-4-102/199_N

Environmental data	
Operation temperature	-65 °C ... 165 °C
Ingress protection (IP Rating)	Mated / IP67

Ordering Information Table		
Item number	Item description	Packaging type
85117843	11_SMA-50-4-102/199_NH	Bulk 100 pcs

Suitable cables	
Cable group	X34 - 4 mm / 50 Ohm X28 - 4 mm / 50 Ohm
Suitable cables	Spuma_240-RS-FR SPUMA_240-FR-01

Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3441 / Date of publication: 10.07.2024 / uncontrolled copy