

LINNEA-O-B

~35° + 70° oval beam optimized for 0.5 mm metal sheet or profile. Variant made from PC.

SPECIFICATION:

Dimensions	285.0 x 40.0 mm
Height	10.5 mm
Fastening	clips
ROHS compliant	yes ⓘ




MATERIALS:

Component	Type	Material	Colour	Finish	Length
LINNEA-O-B	Linear lens	PC	clear		285.0

ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
F15952_LINNEA-O-B » Box size: 398 x 298 x 265 mm	153	36	9	8.0





See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):





LED XP-E
FWHM / FWTM 90.0 + 35.0° / 138.0 + 86.0°
Efficiency 81 %
Peak intensity 0.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files





LED L-iC-282-827-865-011A
FWHM / FWTM 91.0 + 39.0° / 139.0 + 84.0°
Efficiency 83 %
Peak intensity 0.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED LP-282-840-009A 60/300
FWHM / FWTM 91.0 + 39.0° / 139.0 + 85.0°
Efficiency 83 %
Peak intensity 0.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):

Helvar



LED LS-282-840-011A
 FWHM / FWTM 92.0 + 39.0° / 140.0 + 86.0°
 Efficiency 82 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

Helvar



LED LX-282-840-023A
 FWHM / FWTM 91.0 + 39.0° / 139.0 + 86.0°
 Efficiency 83 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

MST | Your solutions

LED LinLED 280x24mm 1100lm 830 2C 30V LINNEA-GC G1
 FWHM / FWTM 88.0 + 37.0° / 137.0 + 83.0°
 Efficiency 82 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):





LED NFSW757H
FWHM / FWTM 92.0 + 41.0° / 140.0 + 89.0°
Efficiency 85 %
Peak intensity 0.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files





LED NFSx757G
FWHM / FWTM 87.0 + 38.0° / 140.0 + 85.0°
Efficiency 81 %
Peak intensity 0.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED PL-LIN-IND-Z1 2800 560x24
FWHM / FWTM 91.0 + 39.0° / 140.0 + 94.0°
Efficiency 87 %
Peak intensity 0.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):

OSRAM
Opto Semiconductors



LED Duris S5 (2 chip)
FWHM / FWTM 90.0 + 38.0° / 138.0 + 86.0°
Efficiency 83 %
Peak intensity 0.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors



LED Duris S5 (Single chip)
FWHM / FWTM 91.0 + 38.0° / 139.0 + 88.0°
Efficiency 85 %
Peak intensity 0.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

PHILIPS

LED Fortimo LED Strip 1ft 1100lm FC HV4 & LV4
FWHM / FWTM 92.0 + 40.0° / 140.0 + 85.0°
Efficiency 83 %
Peak intensity 0.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):

PHILIPS


LED	Fortimo LED Strip 1ft 1100lm FC HV5 & LV5
FWHM / FWTM	89.0 + 38.0° / 140.0 + 92.0°
Efficiency	86 %
Peak intensity	0.7 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files

PHILIPS



LED	Fortimo LED Strip 1ft 650lm FC HV4 & LV4
FWHM / FWTM	93.0 + 40.0° / 140.0 + 85.0°
Efficiency	83 %
Peak intensity	0.7 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files

PHILIPS

LED	Fortimo LED Strip 1ft 650lm FC HV5 & LV5
FWHM / FWTM	85.0 + 33.0° / 136.0 + 90.0°
Efficiency	85 %
Peak intensity	0.8 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	





Light distribution files

OPTICAL RESULTS (MEASURED):

SAMSUNG



LED LM561B Plus
 FWHM / FWTM 88.0 + 37.0° / 137.0 + 83.0°
 Efficiency 82 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

SAMSUNG



LED LT-H282C
 FWHM / FWTM 88.0 + 33.0° / 136.0 + 84.0°
 Efficiency 83 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

SAMSUNG

LED LT-H562C
 FWHM / FWTM 88.0 + 33.0° / 136.0 + 84.0°
 Efficiency 83 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):

SAMSUNG



LED LT-Q282B
 FWHM / FWTM 86.0 + 33.0° / 136.0 + 84.0°
 Efficiency 83 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

SAMSUNG



LED LT-S282H
 FWHM / FWTM 87.0 + 33.0° / 136.0 + 84.0°
 Efficiency 83 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

SAMSUNG

LED LT-S562H
 FWHM / FWTM 87.0 + 33.0° / 136.0 + 84.0°
 Efficiency 83 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):

SAMSUNG



LED LT-V282E
 FWHM / FWTM 87.0 + 33.0° / 136.0 + 84.0°
 Efficiency 83 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

SAMSUNG



LED LT-V562E
 FWHM / FWTM 87.0 + 33.0° / 136.0 + 84.0°
 Efficiency 83 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED SEOUL DC 3030
 FWHM / FWTM 89.0 + 37.0° / 138.0 + 87.0°
 Efficiency 84 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):

TRIDONIC



LED LLE G4 24x280mm 1250lm
FWHM / FWTM 89.0 + 38.0° / 138.0 + 86.0°
Efficiency 83 %
Peak intensity 0.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

TRIDONIC



LED LLE G4 24x280mm 2000lm ADV
FWHM / FWTM 88.0 + 40.0° / 139.0 + 88.0°
Efficiency 83 %
Peak intensity 0.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

TRIDONIC

LED LLE G4 24x280mm 650lm
FWHM / FWTM 90.0 + 39.0° / 138.0 + 87.0°
Efficiency 84 %
Peak intensity 0.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Poznan, Poland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)