

## FEATURES

- wide 2:1 input range
- single & dual output options
- 1500 Vdc isolation
- industry standard pin-out
- ultra compact SMD package
- short circuit protection (continuous)
- wide operating temp: -40°C to +85°C
- supports negative output (dual output model)
- designed to meet EN/BS EN 62368



| MODEL          | input voltage |             | output voltage | output current |          | output power | ripple and noise <sup>1</sup> | efficiency |
|----------------|---------------|-------------|----------------|----------------|----------|--------------|-------------------------------|------------|
|                | typ (Vdc)     | range (Vdc) | (Vdc)          | min (mA)       | max (mA) | max (W)      | max (mVp-p)                   | typ (%)    |
| PQP3-D12-S3-M  | 12            | 9~18        | 3.3            | 38             | 758      | 2.5          | 100                           | 75         |
| PQP3-D12-S5-M  | 12            | 9~18        | 5              | 30             | 600      | 3            | 100                           | 79         |
| PQP3-D12-S12-M | 12            | 9~18        | 12             | 13             | 250      | 3            | 100                           | 82         |
| PQP3-D12-S15-M | 12            | 9~18        | 15             | 10             | 200      | 3            | 100                           | 83         |
| PQP3-D12-S24-M | 12            | 9~18        | 24             | 6              | 125      | 3            | 100                           | 81         |
| PQP3-D24-S3-M  | 24            | 18~36       | 3.3            | 38             | 758      | 2.5          | 100                           | 74         |
| PQP3-D24-S5-M  | 24            | 18~36       | 5              | 30             | 600      | 3            | 100                           | 81         |
| PQP3-D24-S12-M | 24            | 18~36       | 12             | 13             | 250      | 3            | 100                           | 83         |
| PQP3-D24-S15-M | 24            | 18~36       | 15             | 10             | 200      | 3            | 100                           | 83         |
| PQP3-D24-S24-M | 24            | 18~36       | 24             | 6              | 125      | 3            | 100                           | 83         |
| PQP3-D12-D5-M  | 12            | 9~18        | ±5             | ±15            | ±300     | 3            | 100                           | 78         |
| PQP3-D12-D9-M  | 12            | 9~18        | ±9             | ±9             | ±167     | 3            | 100                           | 78         |
| PQP3-D12-D12-M | 12            | 9~18        | ±12            | ±7             | ±125     | 3            | 100                           | 79         |
| PQP3-D12-D15-M | 12            | 9~18        | ±15            | ±5             | ±100     | 3            | 100                           | 79         |
| PQP3-D24-D5-M  | 24            | 18~36       | ±5             | ±15            | ±300     | 3            | 100                           | 78         |
| PQP3-D24-D9-M  | 24            | 18~36       | ±9             | ±9             | ±167     | 3            | 100                           | 80         |
| PQP3-D24-D12-M | 24            | 18~36       | ±12            | ±7             | ±125     | 3            | 100                           | 82         |
| PQP3-D24-D15-M | 24            | 18~36       | ±15            | ±5             | ±100     | 3            | 100                           | 81         |

Notes: 1. Ripple & noise testing condition at nominal input voltage and 5%-100% load, the "tip and barrel" method is used for ripple and noise test, please refer to DC-DC Converter Application Notes for specific information.

**POP3 - DXX - XXX - M**

Base Number      Input Voltage      Output      Output Voltage      Packaging Style  
S = single  
D = dual      SMT

## INPUT

| parameter        | conditions/description  | min  | typ    | max    | units |
|------------------|-------------------------|------|--------|--------|-------|
| input voltage    | 12 Vdc input models     | 9    | 12     | 18     | Vdc   |
|                  | 24 Vdc input models     | 18   | 24     | 36     | Vdc   |
| start-up voltage | 12 Vdc input models     |      |        | 9      | Vdc   |
|                  | 24 Vdc input models     |      |        | 18     | Vdc   |
| surge voltage    | for maximum of 1 second |      |        |        |       |
|                  | 12 Vdc input models     | -0.7 |        | 25     | Vdc   |
|                  | 24 Vdc input models     | -0.7 |        | 50     | Vdc   |
| filter           | capacitance filter      |      |        |        |       |
| current          | 12 Vdc input models     |      | 321/30 | 338/50 | mA    |
|                  | 24 Vdc input models     |      | 156/20 | 165/40 | mA    |

## OUTPUT

| parameter               | conditions/description   | min | typ  | max   | units |
|-------------------------|--------------------------|-----|------|-------|-------|
| line regulation         | min to max Vin           |     | ±0.2 | ±0.5  | %     |
| load regulation         | 5% ~ 100% load           |     | ±0.5 | ±1    | %     |
| set-point accuracy      | 5% ~ 100% load           |     |      |       |       |
|                         | positive outputs         |     | ±1   | ±3    | %     |
|                         | negative outputs         |     | ±3   | ±5    | %     |
| switching frequency     | full load, nominal input |     | 300  |       | kHz   |
| transient response      | 25% load step change     |     | ±2.5 | ±5    | %     |
| temperature coefficient | full load                |     |      | ±0.03 | %/°C  |

## PROTECTIONS

| parameter                | conditions/description    | min | typ | max | units |
|--------------------------|---------------------------|-----|-----|-----|-------|
| short circuit protection | continuous, self-recovery |     |     |     |       |

## SAFETY AND COMPLIANCE

| parameter             | conditions/description                                                          | min  | typ | max | units  |
|-----------------------|---------------------------------------------------------------------------------|------|-----|-----|--------|
| isolation voltage     | input-output electric strength test for 1 minute                                | 1500 |     |     | Vdc    |
| isolation resistance  | input-output insulation at 500 Vdc                                              | 1000 |     |     | MΩ     |
| isolation capacitance | input-output capacitance at 100 KHz / 0.1 V                                     |      | 100 |     | pF     |
| safety approvals      | designed to meet 62368: EN, BS EN                                               |      |     |     |        |
| EMC                   | CISPR32/EN55032 Class B (see recommended circuits)                              |      |     |     |        |
| ESD                   | IEC/EN61000-4-2, Contact ±6K, perf. Criteria B                                  |      |     |     |        |
| radiated immunity     | CISPR32/EN55032                                                                 |      |     |     |        |
| EFT/burst             | IEC/EN61000-4-4, ±2KV, perf. Criteria B (see recommended circuits)              |      |     |     |        |
| surge                 | IEC/EN61000-4-5, line to line ±2KV, perf. Criteria B (see recommended circuits) |      |     |     |        |
| conducted immunity    | IEC/EN61000-4-6 3 Vrms                                                          |      |     |     |        |
| RoHS                  | yes                                                                             |      |     |     |        |
| MTBF                  | MIL-HDBK-217F @ 25°C                                                            | 1000 |     |     | kHours |


## ENVIRONMENTAL

| parameter             | conditions/description | min | typ | max | units |
|-----------------------|------------------------|-----|-----|-----|-------|
| operating temperature |                        | -40 |     | 85  | °C    |
| storage temperature   |                        | -55 |     | 125 | °C    |
| humidity              | non-condensing         | 5   |     | 95  | %     |

## SOLDERABILITY

| parameter        | conditions/description          | min | typ | max | units |
|------------------|---------------------------------|-----|-----|-----|-------|
| hand soldering   | 1.5 mm from case for 10 seconds |     |     | 300 | °C    |
| reflow soldering | 60 s max                        |     |     | 245 | °C    |

## DERATING CURVE



## MECHANICAL



| parameter     | conditions/description                                      | min | typ | max | units |
|---------------|-------------------------------------------------------------|-----|-----|-----|-------|
| dimensions    | 14 x 14 x 9                                                 |     |     |     | mm    |
| case material | Black plastic; flame-retardant and heat-resistant (UL94-V0) |     |     |     |       |
| weight        |                                                             |     | 2.2 |     | g     |

## MECHANICAL DRAWING

units: mm [inches]

pin diameter tolerance:  $\pm 0.10$  [ $\pm 0.004$ ]tolerance:  $\pm 0.50$  [ $\pm 0.020$ ]


| PIN CONNECTIONS |        |      |
|-----------------|--------|------|
| PIN             | Single | Dual |
| 1               | GND    | GND  |
| 4               | Vin    | Vin  |
| 5               | +Vo    | +Vo  |
| 6               | NC     | 0V   |
| 7               | 0V     | -Vo  |



Note: Grid 2.54\*2.54mm


## RECOMMENDED CIRCUITS

**Figure 1**  
Single output



| Parameter Description |            |            |
|-----------------------|------------|------------|
| Vin (Vdc)             | 12         | 24         |
| Cin                   | 47uF/25V   | 47uF/50V   |
| Vo (Vdc)              | 3.3, 5     | 12, 15, 24 |
| Co                    | 100uF/6.3V | 27uF/35V   |


**Figure 2**  
Dual output



| Parameter Description |          |          |
|-----------------------|----------|----------|
| Vin (Vdc)             | 12       | 24       |
| Cin                   | 47uF/50V |          |
| Vo (Vdc)              | 5, 9     | 12, 15   |
| Co                    | 47uF/16V | 10uF/25V |

## EMC COMPLIANCE CIRCUITS

**Figure 3**  
Single output




| Parameter Description |                                                     |   |           |    |    |             |   |           |    |    |
|-----------------------|-----------------------------------------------------|---|-----------|----|----|-------------|---|-----------|----|----|
| Part No.              | Vin: 12 Vdc                                         |   |           |    |    | Vin: 24 Vdc |   |           |    |    |
| Vo (Vdc)              | 3.3                                                 | 5 | 12        | 15 | 24 | 3.3         | 5 | 12        | 15 | 24 |
| FUSE                  | slow blow, choose according to actual input current |   |           |    |    |             |   |           |    |    |
| C0                    | 1000μF/25V                                          |   |           |    |    | 680μF/50V   |   |           |    |    |
| C1                    | 10μF/50V                                            |   | 4.7μF/50V |    |    | 10μF/50V    |   | 4.7μF/50V |    |    |
| LDM1                  | 15μH                                                |   |           |    |    |             |   |           |    |    |
| C2                    | 4.7μF/50V                                           |   |           |    |    |             |   |           |    |    |
| C3                    | 330μF/50V                                           |   |           |    |    |             |   |           |    |    |
| CY1                   | 1nF/2KV                                             |   |           |    |    |             |   |           |    |    |
| C4                    | Refer to the Cout Fig.2                             |   |           |    |    |             |   |           |    |    |

Note: For EMC tests we use Part ① in Fig. 3 for immunity and part ② for emissions test. Selecting based on needs.

## EMC COMPLIANCE CIRCUITS (CONTINUED)

**Figure 4**  
**Dual output**



| Parameter Description |                                                     |           |                  |
|-----------------------|-----------------------------------------------------|-----------|------------------|
| Part No.              | Vin: 12 Vdc                                         |           | Vin: 24 Vdc      |
| Vo (Vdc)              | ±5, ±9, ±12                                         | ±15       | ±5, ±9, ±12, ±15 |
| FUSE                  | slow blow, choose according to actual input current |           |                  |
| C0                    | 1000μF/25V                                          |           | 680μF/50V        |
| C1                    | 4.7μF/50V                                           |           |                  |
| LDM1                  | 10μH                                                |           |                  |
| C2                    | 10μF/50V                                            |           |                  |
| C3                    | 330μF/50V                                           |           |                  |
| CY1                   | 1nF/2KV                                             | 470pF/2KV | 1nF/2KV          |
| CY2                   | 1nF/2KV                                             | 470pF/2KV | 1nF/2KV          |
| CY3                   | 1nF/2KV                                             | 470pF/2KV | /                |
| C4,C5                 | Refer to the Cout Fig.3                             |           |                  |

Note: For EMC tests we use Part ① in Fig. 4 for immunity and part ② for emissions test. Selecting based on needs.

## REVISION HISTORY

| rev. | description                                | date       |
|------|--------------------------------------------|------------|
| 1.0  | initial release                            | 03/28/2020 |
| 1.01 | tolerance update to page 4                 | 06/09/2020 |
| 1.02 | derating curve and circuit figures updated | 07/15/2021 |
| 1.03 | CE certification removed                   | 11/22/2022 |
| 1.04 | dual output circuits added                 | 05/31/2023 |

The revision history provided is for informational purposes only and is believed to be accurate.



**Headquarters**  
20050 SW 112th Ave.  
Tualatin, OR 97062  
**800.275.4899**

Fax 503.612.2383  
**cui.com**  
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.