



0385




0385-0-15-XX-43-XX-10-0
Press-fit in 1,17 mounting hole

4001




4001-0-15-XX-43-XX-04-0
Press-fit in 1,45 mounting hole

1782




1782-0-15-XX-43-XX-04-0
Press-fit in 1,14 mounting hole

5960



5960-0-15-XX-43-XX-04-0
Hex press-fit in 1,45 plated thru hole


1401/3185



Basic Part Number	Depth N	Length L
1401-0	3,68	4,19
3185-0	2,77	3,30


XXXX-0-15-XX-30-XX-10-0
Solder mount in 1,4 min. mounting hole
Also available on 16mm wide carrier tape: 1,700 parts per 330mm reel.
Order as: XXXX-0-57-XX-30-XX-10-0

4310




4310-0-31-XX-43-XX-04-0
Compliant press-fit in 1,02±0,08 plated hole. For 2,29→3,30 thick board.

1385




1385-0-15-XX-43-XX-10-0
Surface mount

3018




3018-0-15-XX-30-XX-04-0
Press-fit in 1,45 mounting hole

8852



8852-0-15-XX-30-XX-04-0
Press-fit in 1,42 mounting hole


3907



3907-0-18-XX-30-XX-10-0
Surface mount
Also available on 12mm wide carrier tape: 4,000 parts per 330mm reel.
Order as: 3907-0-58-XX-30-XX-10-0



P.C.B. Layout



SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±0,13
DIAMETERS: ±0,05
ANGLES: ± 2°

ORDER CODE: XXXX - X - XX - XX - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 5,08µm TIN/LEAD OVER NICKEL
- ◇ 80 5,08µmTIN OVER NICKEL (RoHS)
- ◇ 15 0,25µm GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 02 2,54µm TIN/LEAD OVER NICKEL
- ◇ 84 2,54µm TIN OVER NICKEL (RoHS)
- ◇ 27 0,76µm GOLD OVER NICKEL (RoHS)



SELECT CONTACT

#30, #35 or #43 CONTACT (DATA ON PAGES 219 & 220)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[3185-0-15-01-30-02-10-0](#) [3185-0-15-01-30-27-10-0](#) [1385-0-15-01-43-27-10-0](#) [8852-0-15-80-30-27-04-0](#) [5960-0-15-80-43-27-04-0](#) [3185-0-15-80-30-84-10-0](#) [3185-0-15-80-30-27-10-0](#) [3018-0-15-80-30-84-04-0](#) [1401-0-15-80-30-84-10-0](#)
[1401-0-15-80-30-27-10-0](#) [1385-0-15-80-43-27-10-0](#) [3018-0-15-15-30-27-04-0](#) [5960-0-15-15-43-27-04-0](#)