

COAXIAL FIXED ATTENUATOR, 50 Ohm, 10 dB, BNC
6810.01.A

Properties

- Wide range of interfaces
- Fixed attenuation level from 0 dB up to 40 dB
- 50 Ω or 75 Ω impedance
- Various bandwidth to improve the impedance matching between subsystems of its waveform
- Used in many test and measurement and communication applications.



Product configuration		
Interface	Gender	Standard
BNC	plug (male)	IEC 60169-8_MIL-STD-348A/301_CECC 22120
BNC	jack (female)	IEC 60169-8_MIL-STD-348A/301_CECC 22120

Electrical data	
Impedance	50Ω
Operating frequency	0 GHz ... 4 GHz
Attenuation nominal	10 dB
VSWR	1.2
Return loss	20.8 dB

Electrical Data (frequency related)		
Frequency range	Attenuation deviation	VSWR max
0 GHz to 2 GHz	+/- 0.3 dB	1.1
2 GHz to 4 GHz	+/- 0.5 dB	1.2

Electrical Data (power)	
Average power	1 W at 30 °C ambient temperature. Linearly derated to 0 W at 130 °C ambient temperature.
Peak power	500 W, 5 μs pulse width, 0.05 % duty cycle
Electrical remarks	Peak voltage max. 160V (50 Ohm)

COAXIAL FIXED ATTENUATOR, 50 Ohm, 10 dB, BNC

6810.01.A

Interface and material data		
Interface	BNC / plug (male)	
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Interface	BNC / jack (female)	
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Environmental data	
Operation temperature	-55 °C ... 130°C

Ordering Information Table	
Item number	Item description
22550179	6810.01.A

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P1622 / Date of publication: 23.11.2023 / uncontrolled copy