

# D-Sub M 7W2 ANG FE 20A UNC NM30 BL




Image is for illustration purposes only. Please refer to product description.

Part number	09 69 200 9033
Specification	D-Sub M 7W2 ANG FE 20A UNC NM30 BL
HARTING eCatalogue	<a href="https://b2b.harting.com/09692009033">https://b2b.harting.com/09692009033</a>

## Identification

Category	Connectors
Series	D-Sub
Identification	Mixed
Element	Connector
Description of the contact	Turned Angled

## Version

Termination method	Wave soldering termination
Gender	Female
Size	D-Sub 2
Number of contacts	7
Number of signal contacts	5
Number of power contacts	2
PCB fixing	With frame With board locks
Locking type	Fixing flange with thread 4-40 UNC

## Technical characteristics

Contact spacing (termination side)	2.54 mm
Flange height	7.3 mm
Rated current	5 A
Rated current (power)	20 A
Insulation resistance	>10 <sup>5</sup> Ω



**Pushing Performance**  
Since 1945

## Technical characteristics

Contact resistance, signal area	≤10 mΩ
Contact resistance, power area	≤1 mΩ
Tightening torque	≤0.6 Nm Female screw lock
Limiting temperature	-55 ... +125 °C
Performance level	NM 30 (S4) 1
Mating cycles	≥500
Test voltage $U_{r.m.s.}$	1 kV
Isolation group	IIIa ( $175 \leq CTI < 400$ )
PCB thickness	1.6 mm
Hot plugging	No

## Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled (PBT) Shell: steel, tin plated
Colour (insert)	Green
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated Mating side Sn over Ni Termination side
Layer thickness	≥0.76 μm
Layer thickness	≥30 μinch
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(a) / 6(a)-I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight 6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes



Pushing Performance  
Since 1945

Material properties

California Proposition 65 substances	Antimony trioxide
	Lead
	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	DIN 41652-1
	CECC 75301-802
UL / CSA	UL 1977 ECBT2.E102079

Commercial data

Packaging size	50
Net weight	17 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140097476
ETIM	EC001136
eCl@ss	27440214 D-Sub coupler