

Pushbutton Ø 16 mm silver contact

82-4151.2000.B001



<https://eao.com/p/82-4151.2000.B001>

Your product:



82-4151.2000.B001
Pushbutton Ø 16 mm silver contact

FRONT

Front form:	round
Front bezel shape:	flush
Front bezel material:	Stainless steel
Front dimension:	Ø 18 mm

MOUNTING

Mounting type:	Panel mounting
Mounting cut-out:	Ø 16 mm

OPERATING-/INDICATION PART

Lens shape:	flush
Lens material:	Stainless steel
Lens colour:	Silver
Lens illumination:	non illuminative
Lens optics:	opaque
Symbol:	ON/OFF

ELECTRICAL CHARACTERISTICS

Electrical lifetime:	50 000 cycles of operation
Electric strength:	1500 VAC, 50 Hz 1 minute between live terminals and ground
Contacts:	1 C
Rated insulation voltage Ui:	250 V

Switching voltage and switching current:	according to IEC 60947-5-1 (Silver contacts) Service categorie AC-15	
Voltage	Current	
24 VAC	1 A	
35 VAC	1 A (M12 versio	
110 VAC	1 A	
220 VAC	0.5 A	
Switch rating DC service categorie DC-13 (Silver contacts)		
Voltage	Current	
24 VDC	0.7 A	
35 VDC	0.5 A (M12 vers	
110 VDC	0.2 A	
220 VDC	0.1 A	
according to UL 508 (Silver contacts)		
$\cos\phi$ 0,75 ... 0,8		
Voltage	Current	
120 VAC	5 A	
240 VAC	3 A	
24 VAC	1 A	
Pollution degree:	2, according to EN IEC 60947-1	
Thermal current I_{th}:	5 A	
Rated Operational Voltage U_e:	250 VAC	

MECHANICAL CHARACTERISTIC

Operating force:	4 N ... 7 N
Weight:	0.018 kg
Switching system:	Snap-action switching element
Terminal:	Soldering terminal, 2.8 x 0.5 mm
Mechanical lifetime:	500 000 cycles of operation
Operating Travel:	ca. 3 mm
Tightening torque:	0.5 ... 0.6 Nm
Switching action:	Maintained
Contact material:	Silver

AMBIENT CONDITION

Operating temperature:	- 30 °C ... + 70 °C
Vibration resistance:	10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6
IP front protection:	IP65, IP67
Storage temperature:	- 40 °C ... + 80 °C
Climate resistance:	Damp heat, 21 days according to IEC 60512-11
Shock resistance:	

Max. 500 m / s² as per IEC 60068-2-27

CERTIFICATE

Approbations: CB, CCC, C UL, UL

REACH: REACH compliant


Conformities: CE, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)

RoHS: RoHS compliant


OTHER

Short Description: Pushbutton Ø 16 mm silver contact, Maintained, 1 C, Soldering terminal, 2.8 x 0.5 mm, round, Stainless steel, ON/OFF, Silver


Wiring diagrams:



Component layouts:



Dimension drawings:



A = Solder terminal
B = Screw terminal

Mounting cut-outs:

