



Pushing Performance
Since 1945

D-Sub M 3W3 STR MA 20A UNC NM30 BL



Image is for illustration purposes only. Please refer to product description.

Part number	09 69 200 9147
Specification	D-Sub M 3W3 STR MA 20A UNC NM30 BL
HARTING eCatalogue	https://b2b.harting.com/09692009147

Identification

Category	Connectors
Series	D-Sub
Identification	Mixed
Element	Connector
Description of the contact	Turned Straight

Version

Termination method	Wave soldering termination
Gender	Male
Size	D-Sub 2
Number of contacts	3
Number of signal contacts	0
Number of power contacts	3
PCB fixing	With board locks
Locking type	Fixing flange with thread 4-40 UNC

Technical characteristics

Flange height	7.5 mm
Rated current (power)	20 A
Insulation resistance	$>10^5 \Omega$
Contact resistance, power area	$\leq 1 \text{ m}\Omega$
Tightening torque	$\leq 0.6 \text{ Nm}$ Female screw lock



Pushing Performance
Since 1945

Technical characteristics

Limiting temperature	-55 ... +125 °C
Performance level	NM 30 (S4) 1
Mating cycles	>500
Test voltage $U_{r.m.s.}$	1 kV
Isolation group	IIIa ($175 \leq CTI < 400$)
PCB thickness	1.6 mm
Hot plugging	No

Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled (PBT) Shell: steel, tin plated
Colour (insert)	Green
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated Mating side Sn over Ni Termination side
Layer thickness	$\geq 0.76 \mu\text{m}$
Layer thickness	$\geq 30 \mu\text{inch}$
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26



Pushing Performance
Since 1945

Specifications and approvals

Specifications	DIN 41652-1
	CECC 75301-802
UL / CSA	UL 1977 ECBT2.E102079

Commercial data

Packaging size	50
Net weight	11.92 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140097834
ETIM	EC001136
eCl@ss	27440214 D-Sub coupler