NEO-8Q module

u-blox 8 GPS module

Robust GPS module for easy manufacturing

- High sensitivity of -166 dBm for single GNSS reception
- Cost-efficient system
- TCXO-based product enables fastest time-to-first-fix
- Low power consumption
- Superior anti-spoofing and anti-jamming







2.4 mm Pblox NEO-8Q

12.2 × 16.0 × 2.4 mm

Product description

The NEO-8Q standard precision GNSS module is built on the reliable performance of the u-blox 8 GNSS engine, which receives GPS, GLONASS, QZSS and SBAS signals. The NEO-8Q delivers high sensitivity and minimal acquisition times in the industry proven NEO form factor.

The NEO-8Q features low power consumption and supports advanced Power Save Modes. It also provides message integrity protection, geofencing, spoofing detection, and odometer functionalities.

NEO-8Q is an economical choice for best performance and easier RF integration. For RF optimization the NEO-8Q features an additional front-end LNA for easier antenna integration and a front-end SAW filter for increased jamming immunity. The industry proven NEO form factor allows easy migration from previous NEO generations. Sophisticated RF architecture and interference suppression ensure maximum performance even in GNSS-hostile environments.

The NEO-8Q combines a high level of robustness and integration capability with flexible connectivity options. The DDC (I^2C compliant) interface provides connectivity and enables synergies with most u-blox cellular modules.

u-blox 8 modules use GNSS chips qualified according to AEC-Q100 and are manufactured in ISO/TS 16949 certified sites. Qualification tests are performed as stipulated in the ISO16750 standard: "Road vehicles – Environmental conditions and testing for electrical and electronic equipment".

| | NEO |
|----------------------------------|-----|
| Grade | _ |
| Automotive | |
| Professional | • |
| Standard GNSS | |
| GPS/QZSS | |
| GLONASS | |
| Galileo | |
| BeiDou | |
| Number of concurrent GNSS | 1 |
| Interfaces | |
| UART | 1 |
| USB | 1 |
| SPI | 1 |
| DDC (I ² C compliant) | 1 |
| Features | |
| Additional SAW | • |
| Additional LNA | |
| RTC crystal | |
| Oscillator | т |
| Timepulse | 1 |
| Power supply | |
| 2.7 V – 3.6 V | • |

Ğ

T = TCXO



NEO-8Q module



Features

| Receiver type | 72-channel u-blox GPS L1 C/A, GLOM QZSS L1 C/A SBAS: WAAS, EG | NASS L1 FDMA, |
|--|--|---|
| Nav. update rate | up to 18 Hz | |
| Postition accuracy Autonomous: | GPS 2.5 m CEP | GLONASS 4.0 m CEP |
| Acquisition Cold starts: Aided starts: Reacquisition: | 29 s 2 s 1 s | 30 s 2 s 1 s |
| Sensitivity Tracking & Nav.: Cold starts: Hot starts: | –166 dBm –148 dBm –157 dBm | –166 dBm –145 dBm –156 dBm |
| Assistance GNSS | AssistNow Online AssistNow Offline AssistNow Auton OMA SUPL & 3GF | e (up to 35 days) omous (GPS only, up to 3 days) |
| Oscillator | TCXO | |
| RTC crystal | Built-in | |
| Anti jamming | Active CW detect extra onboard SA | ion and removal; W band pass filter |
| Memory | ROM | |
| Supported antennas | Active and passiv | e |
| Raw Data | Code phase outpu | ut |
| Odometer | Integrated in navi | gation filter |
| Geofencing | Up to 4 circular ar GPIO for waking u | |
| Spoofing detection | Built-in | |
| Signal integrity | Signature feature | with SHA 256 |
| - | | |

Package

24 pin LCC (Leadless Chip Carrier): 12.2 x 16.0 x 2.4 mm, 1.6 g

Environmental data, quality & reliability

| Operating temp. | -40 °C to +85 °C | |
|---|------------------|--|
| Storage temp. | -40 °C to +85 °C | |
| RoHS compliant (lead-free) | | |
| Qualification according to ISO 16750 | | |
| Manufactured in ISO/TS 16949 certified production sites | | |
| Uses u-blox 8 chips qualified according to AEC-Q100 | | |

Interfaces

| Serial interfaces | 1 UART 1 USB V2.0 full speed 12 Mbit/s 1 SPI (optional) 1 DDC (I²C compliant) |
|-------------------|--|
| Digital I/O | Configurable timepulse 1 EXTINT input for Wakeup |
| Timepulse | Configurable: 0.25 Hz to 10 MHz |
| Protocols | NMEA, UBX binary, RTCM |

Support products

| u-blox 8 Evalua | ation Kits: |
|---|---|
| Easy-to-use kits to get familiar with u-blox M8 positioning technology, evaluate functionality, and visualize GNSS performance. | |
| EVK-8N | u-blox 8 GNSS Evaluation Kit, supports TCXO, supports NEO-8Q |

Product variants

| NEO-8Q | u-blox 8 GNSS LCC module, | |
|--------|---------------------------|--|
| | TCXO, ROM, SAW, LNA | |

Electrical data

| Supply voltage | 2.7 V to 3.6 V |
|-----------------------------------|--|
| Power Consumption ¹ | 22 mA @ 3.0 V (Continuous) 10 mA @ 3.0 V Power Save mode (1 Hz) |
| Backup Supply | 1.4 V to 3.6 V |

1 For default mode: GPS incl. QZSS, SBAS

Further information

For contact information, see www.u-blox.com/contact-us.

For more product details and ordering information, see the product data sheet.

Legal Notice:

u-blox reserves all rights to this document and the information contained herein. Products, names, logos and designs described herein may in whole or in part be subject to intellectual property rights. Reproduction, use, modification or disclosure to third parties of this document or any part thereof without the express permission of u-blox is strictly prohibited.

The information contained herein is provided "as is". No warranty of any kind, either express or implied, is made in relation to the accuracy, reliability, fitness for a particular purpose or content of this document. This document may be revised by u-blox at any time. For most recent documents, please visit www.u-blox.com. Copyright © 2018, u-blox AG