

EMG 12-REL/KSR-230/1AU - Relay module



2942616

<https://www.phoenixcontact.com/us/products/2942616>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay module, with soldered-in miniature switching relay, contact (AgPd60 5 µm hard gold-plated): medium to large loads, 1 N/O contact, 230 V AC/DC input voltage

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2942616 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C460 |
| Product key | CK61C2 |
| GTIN | 4017918080792 |
| Weight per piece (including packing) | 45.77 g |
| Weight per piece (excluding packing) | 45.185 g |
| Customs tariff number | 85364900 |
| Country of origin | DE |

EMG 12-REL/KSR-230/1AU - Relay module



2942616

<https://www.phoenixcontact.com/us/products/2942616>

Technical data

Notes

Utilization restriction

| | |
|----------|---|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---|

Product properties

| | |
|-------------------------|--------------------------------|
| Product type | Relay Module |
| Operating mode | 100% operating factor |
| Mechanical service life | approx. 2×10^7 cycles |

Data management status

| | |
|------------------------------|------------|
| Date of last data management | 02.05.2024 |
| Article revision | 08 |

Insulation characteristics

| | |
|----------------------|------------------|
| Insulation | Basic insulation |
| Overvoltage category | III |
| Pollution degree | 2 |

Electrical properties

| | |
|---|--|
| Maximum power dissipation for nominal condition | 1.15 W |
| Test voltage (Winding/contact) | 4 kV AC (50 Hz, 1 min., winding/contact) |

Input data

Coil side

| | |
|--------------------------------|-------------------------------------|
| Nominal input voltage U_N | 230 V AC/DC |
| Input voltage range | 184 V AC/DC ... 253 V AC/DC (20 °C) |
| Drive and function | monostable |
| Drive (polarity) | polarized |
| Typical input current at U_N | 5 mA |
| Typical response time | 6 ms |
| Typical release time | 7 ms |
| Protective circuit | Bridge rectifier; Bridge rectifier |
| Operating voltage display | Yellow LED |

Output data

Switching

| | |
|---------------------------|------------------------------|
| Contact switching type | 1 N/O contact |
| Type of switch contact | Double contact |
| Contact material | AgPd60 5 µm hard gold-plated |
| Maximum switching voltage | 30 V AC |

EMG 12-REL/KSR-230/1AU - Relay module



2942616

<https://www.phoenixcontact.com/us/products/2942616>

| | |
|---------------------------------------|------------------|
| | 36 V DC |
| Limiting continuous current | 0.5 A |
| Maximum inrush current | 0.2 A |
| Interrupting rating (ohmic load) max. | 5 W (at 24 V DC) |

Switching: when the gold layer is destroyed

| | |
|---------------------------------------|--|
| Note | the following values are applicable if a gold layer is destroyed |
| Maximum switching voltage | 125 V AC |
| Minimum switching voltage | 150 V DC |
| Limiting continuous current | 2 A |
| Maximum inrush current | 2 A |
| Interrupting rating (ohmic load) max. | 29 W (at 24 V DC) 29 W (at 48 V DC) 29 W (at 60 V DC) |

Connection data

Coil side

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Conductor cross section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross section AWG | 24 ... 12 |

Contact side

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Conductor cross section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross section AWG | 24 ... 12 |

Dimensions

| | |
|--------|---------|
| Width | 12.5 mm |
| Height | 75 mm |
| Depth | 62.5 mm |

Material specifications

| | |
|-------|------------------|
| Color | green (RAL 6021) |
|-------|------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -20 °C ... 40 °C |
|---------------------------------|------------------|

EMG 12-REL/KSR-230/1AU - Relay module



2942616

<https://www.phoenixcontact.com/us/products/2942616>

| | |
|---|------------------|
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
|---|------------------|

Mounting

| | |
|-------------------|---------------------------|
| Mounting type | DIN rail mounting |
| Assembly note | in rows with zero spacing |
| Mounting position | any |

EMG 12-REL/KSR-230/1AU - Relay module



2942616

<https://www.phoenixcontact.com/us/products/2942616>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2942616>



EAC

Approval ID: RU*C-DE.*08.B.00010

EMG 12-REL/KSR-230/1AU - Relay module



2942616

<https://www.phoenixcontact.com/us/products/2942616>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27371601 |
| ECLASS-12.0 | 27371601 |
| ECLASS-13.0 | 27371601 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001437 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

EMG 12-REL/KSR-230/1AU - Relay module



2942616
<https://www.phoenixcontact.com/us/products/2942616>

Environmental product compliance

| | |
|---|---|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c), 7(a) |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | Hexahydromethylphthalic anhydride(CAS: n/a) |
| | Lead(CAS: 7439-92-1) |
| SCIP | 0953e767-b729-44e5-b2ca-0686e8f8c88b |

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com