


DIMENSIONS



(mm)	Uncoated Nominal:	Coated Min:	Coated Max:
O.D. (A)	26.87	26.49	28.01
I.D. (B)	14.15	13.01	14.53
Ht. (C)	12.24	12.24	13.00
Eff. Parameters			
Ae mm²	le mm	Ve mm³	
73.2	60.2	4410	

INDUCTANCE

AL value (nH/T ²)	Test conditions
15300 ± 30%	10 kHz, 0.5 mT (For N=5, use 0.28 mA), 25°C

LOSS FACTOR

$\tan \delta/\mu$	Production lot limit Max avg	Test conditions
< 3.5 · 10 ⁻⁶	< 3 · 10 ⁻⁶	10 kHz, < 0.25 mT, 25 °C
< 55 · 10 ⁻⁶	< 45 · 10 ⁻⁶	100 kHz, < 0.25 mT, 25 °C

COATING

Epoxy rated for 200°C continuous operation.
Voltage breakdown 2000VDC Min Wire-to-Wire.

NOTE

Spec. modifications	Previous	Revised
2007-08-24	Loss factor: General W material	Loss factor: Detail as indicated