


DIMENSIONS



(mm)	Uncoated Nominal:	Coated Min:	Coated Max:
O.D. (A)	12.70	12.44	12.96
I.D. (B)	8.14	7.67	8.61
Ht. (C)	3.18	3.05	3.31

Eff. Parameters		
$A_e \text{ mm}^2$	$l_e \text{ mm}$	$V_e \text{ mm}^3$
7.1	31.7	226

INDUCTANCE

AL value (nH/T ²)	Test conditions
745 ± 25%	10 kHz, 0.5 mT (For N = 5, use 0.6 mA), 25°C

CORE LOSSES

$P_L \text{ max}$	Production lot limit Max avg	Test conditions
27.8 mW (123 mW/cm ³)	25.3 mW (112 mW/cm ³)	100 kHz, 100 mT, 100°C

COATING

Black Lacquer

NOTE

Spec. Modifications	Previous	Revised