



0077540A7

110 Delta Drive
 Pittsburgh, PA 15238
 NAFTA Sales: (1)800-245-3984
 HK Sales : (852)3102-9337
 magnetics@spang.com



Kool M μ Permeability (μ)	A _L (nH/T ²)	Core Marking			Coating Color
		Lot Number	Part Number	Inductance Grade	
125	217 ± 8%	XXXXXX	77540A7	N/A	Black

Dimensions	Uncoated		Coated Limits			Packaging
	(mm)	(in)	(mm)	(in)		
OD (A)	54.00	2.125	54.90	2.161	max	Cardboard cut-outs Box Qty= 90 pcs
ID (B)	29.00	1.141	28.10	1.106	min	
HT (C)	14.40	0.567	15.30	0.602	max	

Electrical Characteristics			Physical Characteristics						
Watt Loss @ 100kHz, 100mT max (mW/cm ³)	DC Bias min (oersteds)		Voltage Breakdown wire to wire min (V _{AC})	Break Strength min (kg)	Window Area W _a (mm ²)	Cross Section A _e (mm ²)	Path Length L _e (mm)	Volume V _e (mm ³)	Est. Weight (g)
	80%	50%							
1000	14	35	3000	113.0	620	174	126	22,000	136

Winding Information					Temperature Rating	
Winding Length Per Turn				Wound Coil Dimensions (mm)		Curie Temp: 500°C
Winding Factor	(mm)	Winding Factor	(mm)	40% Winding Factor		Coating Temp (Continuous up to): 200°C
				OD	60.9	
				HT	24.3	Notes:
				Max OD	63.9	
				Max HT	36.3	
0%	57.4	40%	72.0	Completely Full Window		
20%	64.7	45%	74.0	Surface Area (mm ²)		
25%	66.5	50%	76.1			
30%	67.9	60%	80.5	Unwound Core	7,500	
35%	70.2	70%	85.5	40% Winding Factor	11,000	

