

General Description

The AGM30P110A combines advanced trench MOSFET technology with a low resistance package to provide extremely low $R_{DS(ON)}$

This device is ideal for load switch and battery protection applications.

Features

- Advance high cell density Trench technology
- Low $R_{DS(ON)}$ to minimize conductive loss
- Low Gate Charge for fast switching
- Low Thermal resistance
- 100% Avalanche tested
- 100% DVDS tested


Application

- MB/VGA Vcore
- SMPS 2nd Synchronous Rectifier
- POL application
- BLDC Motor driver

Product Summary

BVDSS	RDS(ON)	ID
-30V	2.8mΩ	-138A

PDFN5*6 Pin Configuration



Package Marking and Ordering Information

Device Marking	Device	Device Package	Reel Size	Tape width	Quantity
AGM30P110A	AGM30P110A	PDFN5*6	330mm	12mm	3000

Table 1. Absolute Maximum Ratings (TA=25°C)

Symbol	Parameter	Value	Unit
VDS	Drain-Source Voltage (VGS=0V)	-30	V
VGS	Gate-Source Voltage (VDS=0V)	±20	V
ID	Drain Current-Continuous(Tc=25°C) (Note 1)	-138	A
	Drain Current-Continuous(Tc=100°C)	-83	A
IDM (pluse)	Drain Current-Pulsed (Note 2)	-552	A
PD	Maximum Power Dissipation(Tc=25°C)	138	w
	Maximum Power Dissipation(Tc=100°C)	55.5	w
EAS	Avalanche energy (Note 3)	529	mJ
TJ,TSTG	Operating Junction and Storage Temperature Range	-55 To 150	°C

Table 2. Thermal Characteristic

Symbol	Parameter	Typ	Max	Unit
RθJA	Thermal Resistance Junction-ambient (Steady State) ¹	---	20	°C/W
RθJC	Thermal Resistance Junction-Case ¹	---	0.9	°C/W







Table 3. Electrical Characteristics (TJ=25°C unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
On/Off States						
BVDSS	Drain-Source Breakdown Voltage	VGS=0V ID=-250μA	-30	--	--	V
IDSS	Zero Gate Voltage Drain Current	VDS=-30V,VGS=0V	--	--	-1	μA
IGSS	Gate-Body Leakage Current	VGS=±20V,VDS=0V	--	--	±100	nA
VGS(th)	Gate Threshold Voltage	VDS=VGS,ID=-250μA	-1.2	-1.6	-2.2	V
gFS	Forward Transconductance	VDS=-5V,ID=-15A	--	47	--	S
RDS(on)	Drain-Source On-State Resistance	VGS=-10V, ID=-20A	--	2.8	4.7	mΩ
		VGS=-4.5V, ID=-15A	--	4.5	6.5	mΩ
Dynamic Characteristics						
Ciss	Input Capacitance	VDS=-15V,VGS=0V, F=1MHZ	--	5200	--	pF
Coss	Output Capacitance		--	1100	--	pF
Crss	Reverse Transfer Capacitance		--	920	--	pF
Rg	Gate resistance	VGS=0V, VDS=0V,f=1.0MHz	--	3.5	--	Ω
Switching Times						
td(on)	Turn-on Delay Time	VGS=-10V,VDS=-15V, ID=-30A,RGEN=3Ω	--	25	--	nS
tr	Turn-on Rise Time		--	35	--	nS
td(off)	Turn-Off Delay Time		--	99	--	nS
tf	Turn-Off Fall Time		--	50	--	nS
Qg	Total Gate Charge	VGS=-10V, VDS=-15V, ID=-30A	--	150	--	nC
Qgs	Gate-Source Charge		--	24	--	nC
Qgd	Gate-Drain Charge		--	23	--	nC
Source-Drain Diode Characteristics						
ISD	Source-Drain Current(Body Diode)		--	--	-138	A
VSD	Forward on Voltage	VGS=0V,IS=-20A	--	-0.8	-1.2	V
trr	Reverse Recovery Time	Isd=-20A ,	--	52	--	ns
Qrr	Reverse Recovery Charge	dl/dt=100A/μs , TJ=25℃	--	53	--	nc

Notes 1.The maximum current rating is package limited.

Notes 2.Repetitive Rating: Pulse width limited by maximum junction temperature

Notes 3.EAS condition: TJ=25°C, VDD=-20V, Vgs=-10V, ID=-46A, L=0.5mH, RG=25ohm


Fig.1 Typical Output Characteristics

Fig.2 Continuous Drain Current vs. T_C

Fig.3 Normalized $R_{DS(on)}$ vs. T_J

Fig.4 Normalized V_{th} vs. T_J

Fig.5 Turn-On Resistance vs. V_{GS}

Fig.6 Turn-On Resistance vs. I_D




Fig.7 Capacitance Characteristics




Fig.8 Gate Charge Characteristics




Fig.9 Normalized Transient Impedance




Fig.10 Maximum Safe Operation Area




Fig.11 Switching Time Waveform









Fig.12 Gate Charge Waveform


Dimensions (PDFN5*6)



SYMBOL	MILLIMETER		
	MIN	Typ.	MAX
A	0.900	1.000	1.100
A1	0.254 REF.		
A2	0°0.05		
D	4.824	4.900	4.976
D1	1.605	1.705	1.805
D2	0.500	0.600	0.700
D3	4.924	5.000	5.076
E	5.924	6.000	6.076
E1	3.375	3.475	3.575
E2	5.674	5.750	5.826
b	0.350	0.400	0.450
e	1.270 TYP.		
L	0.534	0.610	0.686
L1	0.424	0.500	0.576
L2	1.800 REF.		
k	1.190	1.290	1.390
H	0.549	0.625	0.701
θ	8°	10°	12°
φ	1.100	1.200	1.300
d			0.100




Symbol	Millimeters		
	MIN.	NOM.	MAX.
A	0.90	1.05	1.20
b	0.35	0.40	0.50
C	0.20	0.25	0.35
D	4.90	5.05	5.20
D1/D2	1.51	1.61	1.71
d	0.50	0.60	0.70
E	6.00	6.15	6.30
E1	5.60	5.75	5.90
E2	3.47	3.57	3.67
e	1.27 BSC.		
H	0.48	0.58	0.68
K	1.17	1.27	1.37
L	0.64	0.74	0.84
L1/L2	0.20 REF.		
θ	8°	10°	12°
M	0.08 REF.		
N	0	-	0.15
O	0.25 REF.		
P	1.28 REF.		




PDFN5*6

Marking Instructions:

Model1:



Model2:



Disclaimer:

The information provided in this document is believed to be accurate and reliable. however,Shenzhen Core Control Electronics Technology Co., Ltd. does not assume any responsibility for the following consequences.Do not consider the use of such information or use beyond its scope.

The information mentioned in this document may be changed at any time without notice.

The products and information provided in this document do not infringe patents. Shenzhen Core Control Electronics Technology Co., Ltd. assumes no responsibility for any infringement of any other rights of third parties.The result of using such products and information.

This document is the fifth version issued on March 10th, 2024. This document replaces all previously provided information.

 It is a registered trademark of Shenzhen Core Control Electronics Technology Co., Ltd.

Copyright © 2017 Shenzhen Core Control Electronics Technology Co., Ltd. all rights reserved.