

# SPE-T1-STRM-90-LED - SPE PCB connector



1215778

<https://www.phoenixcontact.com/us/products/1215778>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



SPE PCB connector, design: IEC 63171-2, degree of protection: IP20, number of positions: 2, 1 Gbps, CAT B (ISO/IEC 63171), material: Plastic, connection method: THR solder connection, cable outlet: straight, Single Pair Ethernet

## Your advantages

- Connectors in accordance with IEC 63171-2
- THR solderable
- Robust industrial design
- THR solderable
- Data transmission up to 600 MHz

## Commercial data

Item number	1215778
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AB13
Product key	ABNBBA
GTIN	4063151296742
Weight per piece (including packing)	5.91 g
Weight per piece (excluding packing)	5.91 g
Customs tariff number	85366930
Country of origin	DE

# SPE-T1-STRM-90-LED - SPE PCB connector



1215778

<https://www.phoenixcontact.com/us/products/1215778>

## Technical data

### Product properties

Product type	Data connector (device side)
Type	SPE
Sensor type	Single Pair Ethernet
Number of positions	2
Connection profile	SPE
Type of packaging	Tape and Reel
Pitch	7.62 mm
Number of slots	1
Shielded	yes
Cable outlet	straight
LED	yes

### Data management status

Article revision	01
------------------	----

### Insulation characteristics

Overvoltage category	I
Degree of pollution	2

### Electrical properties

Rated voltage (III/2)	72 V DC
Rated surge voltage	2250 V DC
Rated surge voltage (III/2)	1500 V
Rated current	4 A
Frequency range	600 MHz
Insulation resistance	> 1 TΩ
Transmission medium	Copper
Transmission characteristics (category)	CAT B (IEC 63171)
Transmission speed	1 Gbps
Power transmission	PoDL

### Connection data

#### Connection technology

Connection method	THR solder connection
-------------------	-----------------------

### Dimensions

Width	7.52 mm
Height	13.33 mm
Length	20.6 mm

### Material specifications

# SPE-T1-STRM-90-LED - SPE PCB connector

1215778

<https://www.phoenixcontact.com/us/products/1215778>



Flammability rating according to UL 94	V0
Housing material	Plastic
Contact material	Copper alloy
Contact surface material	Ni/Au
Contact carrier material	LCP

## Cable/line

Test voltage Core/Core	1000 V DC
Test voltage Core/Shield	2250.00 V DC
Resistance to oil	yes
Flame resistance	UL 94 V0

## Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 750
Insertion force per signal contact	< 1.50 N
Extraction force per signal contact	< 1.5 N

## Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP20
	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Resistance to oil	yes

## Standards and regulations

Flame resistance	UL 94 V0
Resistance to oil	yes

## Mounting

Mounting type	THR soldering
---------------	---------------

Processing notes	
Moisture Sensitive Level	MSL 1

# SPE-T1-STRM-90-LED - SPE PCB connector


1215778

<https://www.phoenixcontact.com/us/products/1215778>



## Drawings

Diagram



Classification reflow soldering profile

# SPE-T1-STRM-90-LED - SPE PCB connector

1215778

<https://www.phoenixcontact.com/us/products/1215778>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1215778>

cULus Recognized				
Approval ID: E335024-20220331				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
	60 V	1.4 A	-	-

# SPE-T1-STRM-90-LED - SPE PCB connector

1215778

<https://www.phoenixcontact.com/us/products/1215778>



## Classifications

### ECLASS

ECLASS-11.0	27440390
ECLASS-13.0	27460201
ECLASS-12.0	27440390

### ETIM

ETIM 9.0	EC002637
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SPE-T1-STRM-90-LED - SPE PCB connector

1215778

<https://www.phoenixcontact.com/us/products/1215778>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)