

Standard Rectifier Module

$$V_{RRM} = 2 \times 1400 \text{ V}$$

$$I_{FAV} = 120 \text{ A}$$

$$V_F = 1.13 \text{ V}$$

Phase leg

Part number

MDD95-14N1B



Backside: isolated

 E72873



Features / Advantages:

- Package with DCB ceramic
- Improved temperature and power cycling
- Planar passivated chips
- Very low forward voltage drop
- Very low leakage current

Applications:

- Diode for main rectification
- For single and three phase bridge configurations
- Supplies for DC power equipment
- Input rectifiers for PWM inverter
- Battery DC power supplies
- Field supply for DC motors

Package: TO-240AA

- Isolation Voltage: 4800 V~
- Industry standard outline
- RoHS compliant
- Height: 30 mm
- Base plate: DCB ceramic
- Reduced weight
- Advanced power cycling

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

Rectifier				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
V_{RSM}	max. non-repetitive reverse blocking voltage	$T_{VJ} = 25^{\circ}\text{C}$				1500	V
V_{RRM}	max. repetitive reverse blocking voltage	$T_{VJ} = 25^{\circ}\text{C}$				1400	V
I_R	reverse current	$V_R = 1400\text{ V}$	$T_{VJ} = 25^{\circ}\text{C}$			200	μA
		$V_R = 1400\text{ V}$	$T_{VJ} = 150^{\circ}\text{C}$			15	mA
V_F	forward voltage drop	$I_F = 150\text{ A}$	$T_{VJ} = 25^{\circ}\text{C}$			1.20	V
		$I_F = 300\text{ A}$				1.43	V
		$I_F = 150\text{ A}$	$T_{VJ} = 125^{\circ}\text{C}$			1.13	V
		$I_F = 300\text{ A}$				1.46	V
I_{FAV}	average forward current	$T_C = 100^{\circ}\text{C}$	$T_{VJ} = 150^{\circ}\text{C}$			120	A
$I_{F(RMS)}$	RMS forward current	180° sine				180	A
V_{F0}	threshold voltage	} for power loss calculation only	$T_{VJ} = 150^{\circ}\text{C}$			0.75	V
r_F	slope resistance					1.95	m Ω
R_{thJC}	thermal resistance junction to case					0.26	K/W
R_{thCH}	thermal resistance case to heatsink				0.2		K/W
P_{tot}	total power dissipation		$T_C = 25^{\circ}\text{C}$			481	W
I_{FSM}	max. forward surge current	$t = 10\text{ ms}; (50\text{ Hz}), \text{ sine}$	$T_{VJ} = 45^{\circ}\text{C}$			2.80	kA
		$t = 8,3\text{ ms}; (60\text{ Hz}), \text{ sine}$	$V_R = 0\text{ V}$			3.03	kA
		$t = 10\text{ ms}; (50\text{ Hz}), \text{ sine}$	$T_{VJ} = 150^{\circ}\text{C}$			2.38	kA
		$t = 8,3\text{ ms}; (60\text{ Hz}), \text{ sine}$	$V_R = 0\text{ V}$			2.57	kA
I^2t	value for fusing	$t = 10\text{ ms}; (50\text{ Hz}), \text{ sine}$	$T_{VJ} = 45^{\circ}\text{C}$			39.2	kA ² s
		$t = 8,3\text{ ms}; (60\text{ Hz}), \text{ sine}$	$V_R = 0\text{ V}$			38.1	kA ² s
		$t = 10\text{ ms}; (50\text{ Hz}), \text{ sine}$	$T_{VJ} = 150^{\circ}\text{C}$			28.3	kA ² s
		$t = 8,3\text{ ms}; (60\text{ Hz}), \text{ sine}$	$V_R = 0\text{ V}$			27.5	kA ² s
C_J	junction capacitance	$V_R = 400\text{ V}; f = 1\text{ MHz}$	$T_{VJ} = 25^{\circ}\text{C}$		116		pF

Package TO-240AA				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
I_{RMS}	RMS current	per terminal				200	A
T_{VJ}	virtual junction temperature			-40		150	°C
T_{op}	operation temperature			-40		125	°C
T_{stg}	storage temperature			-40		125	°C
Weight					76		g
M_D	mounting torque			2.5		4	Nm
M_T	terminal torque			2.5		4	Nm
$d_{Spp/App}$	creepage distance on surface striking distance through air	terminal to terminal	13.0	9.7			mm
$d_{Spb/Apb}$		terminal to backside	16.0	16.0			mm
V_{ISOL}	isolation voltage	t = 1 second	50/60 Hz, RMS; $I_{ISOL} \leq 1$ mA	4800			V
		t = 1 minute		4000			V



Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	MDD95-14N1B	MDD95-14N1B	Box	36	453153

Similar Part	Package	Voltage class
MDD95-08N1B	TO-240AA	800
MDD95-12N1B	TO-240AA	1200
MDD95-16N1B	TO-240AA	1600
MDD95-18N1B	TO-240AA	1800

Equivalent Circuits for Simulation

* on die level

$T_{VJ} = 150^{\circ}\text{C}$



Rectifier

$V_{0\max}$ threshold voltage

0.75

V


$R_{0\max}$ slope resistance *

0.76

mΩ

Technical drawing of a 5-pin DIN connector. The drawing shows the front and side views with the following dimensions:

- Overall length: 92 ± 0.5
- Length from first pin center to end: 80 ± 0.3
- End flange thickness: 6
- Overall height: 20.8 ± 0.25
- Pin 1 height: 14.8
- Pin 2 height: 10 ± 0.1
- Pin 3 height: 5.5 ± 0.1
- Pin 4 height: 5
- Pin 5 height: 4
- Pin 6 height: 7
- Pin 7 height: 6
- Pin 8 height: 5
- Pin 9 height: 4
- Pin 10 height: 3
- Pin 11 height: 2
- Pin 12 height: 1
- Pin 13 height: 0
- Pin 14 height: 0
- Pin 15 height: 0
- Pin 16 height: 0
- Pin 17 height: 0
- Pin 18 height: 0
- Pin 19 height: 0
- Pin 20 height: 0
- Pin 21 height: 0
- Pin 22 height: 0
- Pin 23 height: 0
- Pin 24 height: 0
- Pin 25 height: 0
- Pin 26 height: 0
- Pin 27 height: 0
- Pin 28 height: 0
- Pin 29 height: 0
- Pin 30 height: 0
- Pin 31 height: 0
- Pin 32 height: 0
- Pin 33 height: 0
- Pin 34 height: 0
- Pin 35 height: 0
- Pin 36 height: 0
- Pin 37 height: 0
- Pin 38 height: 0
- Pin 39 height: 0
- Pin 40 height: 0
- Pin 41 height: 0
- Pin 42 height: 0
- Pin 43 height: 0
- Pin 44 height: 0
- Pin 45 height: 0
- Pin 46 height: 0
- Pin 47 height: 0
- Pin 48 height: 0
- Pin 49 height: 0
- Pin 50 height: 0
- Pin 51 height: 0
- Pin 52 height: 0
- Pin 53 height: 0
- Pin 54 height: 0
- Pin 55 height: 0
- Pin 56 height: 0
- Pin 57 height: 0
- Pin 58 height: 0
- Pin 59 height: 0
- Pin 60 height: 0
- Pin 61 height: 0
- Pin 62 height: 0
- Pin 63 height: 0
- Pin 64 height: 0
- Pin 65 height: 0
- Pin 66 height: 0
- Pin 67 height: 0
- Pin 68 height: 0
- Pin 69 height: 0
- Pin 70 height: 0
- Pin 71 height: 0
- Pin 72 height: 0
- Pin 73 height: 0
- Pin 74 height: 0
- Pin 75 height: 0
- Pin 76 height: 0
- Pin 77 height: 0
- Pin 78 height: 0
- Pin 79 height: 0
- Pin 80 height: 0
- Pin 81 height: 0
- Pin 82 height: 0
- Pin 83 height: 0
- Pin 84 height: 0
- Pin 85 height: 0
- Pin 86 height: 0
- Pin 87 height: 0
- Pin 88 height: 0
- Pin 89 height: 0
- Pin 90 height: 0
- Pin 91 height: 0
- Pin 92 height: 0
- Pin 93 height: 0
- Pin 94 height: 0
- Pin 95 height: 0
- Pin 96 height: 0
- Pin 97 height: 0
- Pin 98 height: 0
- Pin 99 height: 0
- Pin 100 height: 0



Rectifier



Fig. 1 Surge overload current
 I_{TSM} , I_{FSM} : Crest value, t : duration




Fig. 2 I^2t versus time (1-10 ms)



Fig. 3 Maximum forward current at case temperature



Fig. 4 Power dissipation vs. onstate current and ambient temperature (per diode)



Fig. 6 Single phase rectifier bridge: Power dissipation versus direct output current and ambient temperature; R = resistive load, L = inductive load


Rectifier


Fig. 6 Three phase rectifier bridge: Power dissipation versus direct output current and ambient temperature




Fig. 7 Transient thermal impedance junction to case (per diode)

R_{thJC} for various conduction angles d:

d	R_{thJC} [K/W]
DC	0.26
180°	0.28
120°	0.30
60°	0.34
30°	0.38

Constants for Z_{thJC} calculation:

i	R_{thi} [K/W]	t_i [s]
1	0.013	0.0012
2	0.072	0.0470
3	0.175	0.3940




Fig. 8 Transient thermal impedance junction to heatsink (per thyristor)

R_{thJK} for various conduction angles d:

d	R_{thJK} [K/W]
DC	0.46
180°	0.48
120°	0.50
60°	0.54
30°	0.58

Constants for Z_{thJK} calculation:

i	R_{thi} [K/W]	t_i [s]
1	0.013	0.0012
2	0.072	0.0470
3	0.175	0.3940
4	0.200	1.3200