







NOTES:

备注

- 1.Copper,nickel base,matte tin
黄铜H62, 镍底, 镀雾锡
- 2.Wire screw hole M5
压线螺孔M5
- 3.Current Rating: 70A
额定电流: 70A
- 4.Operating temperature: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$
工作温度: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$
- 5.There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 6.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差

Ordering Information

HC - * * * * - D * * * * - 02

Type	Screw Thread	Welding Feet	T=Anti Twist	Series	D=Pin	Product No.	Material
M=Pull Teeth (抽牙)	S=M5 (螺牙)	1620-16x20mm	(防止扭动)	0808-8x8mm	S=MT S=MT Dip	产品序号	默认=Copper (黄铜)
RS=Rivet Nut (铆螺母)	4=M4 (螺牙)	2-2个					默认=Copper (黄铜)
RG=Rivet Gasket (铆垫片)	S=M5 (螺牙)	4-4个					默认=Copper (黄铜)
	6=M6 (螺牙)	6-6个					默认=Copper (黄铜)

			GENERAL TOLERANCE	制图	02	深圳市华灿天禄电子有限公司			
			DIM TOL	审核		ShenzhenhuacantianluELECTRONICS CO.,LTD			
			5 or more ± 0.35	批准		产品名称	PCB 焊接端子 插板 铆垫片 M5 4焊脚 11.5x9.2x12.5mm	版本	A
			2~5 ± 0.25	比例		产品料号	HC-RG54-1109-D058-02	单位	mm
1	初版发行		0~2 ± 0.15	SCALE		PART NO.		UNITS	
序号	变更内容	日期	Angle $\pm 3.0^{\circ}$	投影		材料		页次	1/1
No.	MODIFY CONTENT	MODIFY DATE		Projection		MATERIAL		SHEET	