



Rating:
 7A 125V AC UL cUL
 2.5A 250V AC VDE 3C KC
 Insert And Extract Force: 1.36kgf~6.8kgf
 Terminal Strength: ≥60N
 Operating Life: ≥6000 cycles
 Withstand Voltage: Between all terminals: 2500VAC (50-60Hz) 1min
 Terminals to Base: 3750V AC (50-60Hz) 1min
 Leakage Current: 1mA
 Insulation Resistance: ≥100MΩ 500V DC
 Body Material: NYLON66 94V-2~0

| 序号 | 名称 | 材料 | 处理 | 数量 | 备注 |
|----|-------------|--------|----|----|----|
| 1 | DB-6-1塑料件 | 环阻PA66 | 黑色 | 1 | |
| 2 | DB-6-N1L长插销 | 黄铜 | 镀镍 | 1 | |
| 3 | DB-8-1DX短插销 | 黄铜 | 镀镍 | 2 | |
| 4 | DB-6-P4端子 | 黄铜 | 镀锡 | 1 | |
| 5 | DB-6-P3端子 | 黄铜 | 镀锡 | 2 | |

普通公差:
 COMMON TOLERANCE :

深圳市华灿天禄电子有限公司

| | | | | | | | | |
|---------------|----------------------|----------------|-----------|-------------------|--------------------|-----------------|-------------|------|
| UP TO 5 | ±0.20 | 单位 UNIT | mm | 投影 PROJECTED | 品名 PRODUCT NAME | Ac Inlet C6型 | 比例 SCALE | Free |
| ABOVE 5 TO 30 | ±0.30 | 绘图 DRAWN BY | 金泽杰 | 核对 CHECKED BY | 张立龙 | 型号 MODEL NO. | DB-6 | |
| ABOVE 30 | ±0.50 | 日期 DATE | 2022.11.3 | 核准 APPROVAL BY | 王天健 | 料号 PART NO. | DB-6-1P4P3 | |
| REV. DATE | REVISION DESCRIPTION | ISSUE | ANGULAR | ±5° | | | | |