
PART NUMBER**74LS794N**

**Rochester Electronics
Manufactured Components**

Rochester branded components are manufactured using either die/wafers purchased from the original suppliers or Rochester wafers recreated from the original IP. All re-creations are done with the approval of the Original Component Manufacturer. (OCM)

Parts are tested using original factory test programs or Rochester developed test solutions to guarantee product meets or exceeds the OCM data sheet.

Quality Overview

- ISO-9001
- AS9120 certification
- Qualified Manufacturers List (QML) MIL-PRF-38535
 - Class Q Military
 - Class V Space Level

Qualified Suppliers List of Distributors (QSLD)

- Rochester is a critical supplier to DLA and meets all industry and DLA standards.

Rochester Electronics, LLC is committed to supplying products that satisfy customer expectations for quality and are equal to those originally supplied by industry manufacturers.

The original manufacturer's datasheet accompanying this document reflects the performance and specifications of the Rochester manufactured version of this device. Rochester Electronics guarantees the performance of its semiconductor products to the original OCM specifications. 'Typical' values are for reference purposes only. Certain minimum or maximum ratings may be based on product characterization, design, simulation, or sample testing.

8-Bit Latch/Register with Readback


SN54/74LS793 SN54/74LS794

Features/Benefits

- I/O port configuration enables output data back onto input bus
- 8-bit data path matches byte boundaries
- Ideal for microprocessor interface

Description

These 8-bit latches/registers are useful for I/O operations on a microprocessor bus. An image of the output data can be read back by the CPU. This operation is important in control algorithms which make decisions based on the previous status of output controls. Rather than storing a redundant copy of the output data in memory, simply reading the register as an I/O port allows the data to be retrieved from where it has been stored in an 'LS793/4, for verification and/or updating.



The data is loaded in the registers on the low-to-high transition of the clock (CK), for the 'LS794. The data is passed through the 'LS793 when the gate, (G), is High, and it is "latched" when G changes to Low. The output enable, \overline{OE} is used to enable data on D7-D0. When \overline{OE} is low the output of the latches/registers is enabled on D0-D7, enabling D as an output bus so that the host can perform a read operation. When \overline{OE} is High, D7-D0 are inputs to the latches/registers configuring D as an input bus.

The output drive of these commercial parts for any output pin is $I_{OL} = 24$ mA.

'LS793 Function Table

G	\overline{OE}	Q	D
L	L	Q_0^{**}	Output, Q
L	H	Q_0^{**}	Input
H^\dagger	L	D^*	Output, Q*
H	H	D	Input

* In this case the output of the latch feeds the input, and a "race" condition results.


** Q_0 represents the previous "latched" state.

† This transition is not a normal mode of operation and may produce hazards.

Ordering Information

PART NUMBER	PKG	TEMP	POLARITY	TYPE	POWER
SN54LS793	J,W,L	Mil	Non-invert	Latch	LS
SN74LS793	N,J,NL	Com		Register	
SN54LS794	J,W,L	Mil	Non-invert	Latch	LS
SN74LS794	N,J,NL	Com		Register	

Logic Symbols





'LS794 Function Table



CK	\overline{OE}	Q	D
L or H or \downarrow	L	Q_0	Output, Q
L or H or \downarrow	H	Q_0	Input
\uparrow	L	Q_0	Output, Q*
\uparrow	H	D	Input

* In this case the output of the register is clocked to the inputs and the overall Q output is unchanged at Q_0 .

Pin Configurations



IEEE Symbols



Absolute Maximum Ratings

Supply voltage V_{CC}	-0.5 V to 7 V
Input voltage	-1.5 V to 7 V
Off-state output voltage	-0.5 V to 5.5 V
Storage temperature	-65°C to +150°C

Operating Conditions

Operating Conditions											
SYMBOL	PARAMETER				MILITARY MIN TYP MAX			COMMERCIAL MIN TYP MAX			UNIT
V _{CC}	Supply voltage				4.5	5	5.5	4.75	5	5.25	V
T _A	Operating free air temperature				-55			0			75 °C
t _w	Width of Clock/Gate		High		15			15			ns
			Low ('LS794 only)		15			15			
t _{su}	Setup time			'LS793	15↓			10↓			ns
				'LS794	15↑			15↑			
t _h	Hold time			'LS793	10↓			10↓			
				'LS794	0↑			0↑			

↑ ↓ The arrow indicates the transition of the clock/gate input used for reference. ↑ for the low-to-high transitions, ↓ for the high-to-low transitions.

Electrical Characteristics Over Operating Conditions

SYMBOL	PARAMETER		TEST CONDITIONS		MILITARY MIN TYP MAX		COMMERCIAL MIN TYP MAX		UNIT
V_{IL}	Low-level input voltage				0.7		0.8		V
V_{IH}	High-level input voltage				2		2		V
V_{IC}	Input clamp voltage		$V_{CC} = \text{MIN}$	$I_I = -18 \text{ mA}$	-1.5		-1.5		V
I_{IL}	Low-level input current		$V_{CC} = \text{MAX}$	$V_I = 0.4 \text{ V}$	-250		-250		μA
I_{IH}	High-level input current		$V_{CC} = \text{MAX}$	$V_I = 2.7 \text{ V}$	40		40		μA
I_I	Maximum input current	D or Q	$V_{CC} = \text{MAX}$	$V_I = 5.5 \text{ V}$	0.1		0.1		mA
		All others		$V_I = 7 \text{ V}$					
V_{OL}	Low-level output voltage		$V_{CC} = \text{MIN}$ $V_{IL} = \text{MAX}$ $V_{IH} = 2 \text{ V}$	$I_{OL} = 12 \text{ mA}$	0.25	0.4	0.25	0.4	V
				$I_{OL} = 24 \text{ mA}$			0.35	0.5	
V_{OH}	High-level output voltage		$V_{CC} = \text{MIN}$ $V_{IL} = \text{MAX}$ $V_{IH} = 2 \text{ V}$	$I_{OH} = -1 \text{ mA}$	2.4	3.4			V
				$I_{OH} = -2.6 \text{ mA}$			2.4	3.1	
I_{OZL}	Off-state output current		$V_{CC} = \text{MAX}$ $V_{IL} = \text{MAX}$ $V_{IH} = 2 \text{ V}$	$V_O = 0.4 \text{ V}$	-250		-250		μA
I_{OZH}				$V_O = 2.7 \text{ V}$	40		40		
I_{OS}	Output short-circuit current*		$V_{CC} = \text{MAX}$		-30	-130	-30	-130	mA
I_{CC}	Supply current		$V_{CC} = \text{MAX}$ Outputs open	'LS793	120		120		mA
				'LS794	120		120		

* Not more than one output should be shorted at a time and duration of the short-circuit should not exceed one second.

Copyright © Each Manufacturing Company.

All Datasheets cannot be modified without permission.

This datasheet has been download from :

www.AllDataSheet.com

100% Free DataSheet Search Site.

Free Download.

No Register.

Fast Search System.

www.AllDataSheet.com