

DIMENSIONS ARE IN INCHES

UNLESS OTHERWISE NOTED

TOLERANCES ARE:


ONE PLACE DECIMALS $\pm .1$ [2.5] THREE PLACE DECIMALS $\pm .005$ [.13]
TWO PLACE DECIMALS $\pm .01$ [.3] FOUR PLACE DECIMALS $\pm .0010$ [.025]

ANGLES
 $\pm 1^\circ$


TITLE:
2mm C.L. SHROUDED
TERMINAL STRIP TO
MATE WITH CABLE

DWG NO:

STMM-1XX-XX-XX-D-XX-XX
SHEET 1 OF 3



THROUGH HOLE
FIG. 1



STMM-1XX-XX-XX-D-XX-XX

NO. OF POSITIONS
-02 THRU -25

TERMINAL STYLE
-01 IS STANDARD
(.100 [2.54] POST HEIGHT). LEAD STYLE -02
IS FOR MATING WITH TCS ONLY
(.120 [3.05] POST HEIGHT) (SEE TABLE 1)

PLATING SPECIFICATIONS

-G: GOLD (USE T-1S13-XX-G-2)
-T: TIN (USE T-1S13-XX-T-2)
-S: SELECTIVE (USE T-1S13-XX-S-2)
-L: LIGHT SELECTIVE (USE T-1S13-XX-L-2)
-F: FLASH GOLD SELECTIVE (USE T-1S13-XX-F-2)
-H: HEAVY GOLD (USE T-1S13-XX-H-2)
-SM: HEAVY GOLD SELECTIVE, MATTE TIN TAIL (USE T-1S13-XX-S-2)
-TM: MATTE TIN (USE T-1S13-XX-T-2)
-LM: LIGHT GOLD SELECTIVE, MATTE TIN TAIL (USE T-1S13-XX-L-2)
-FM: FLASH GOLD SELECTIVE, MATTE TIN TAIL (USE T-1S13-XX-F-2)

POLARIZED OPTION
XX = PIN NO TO BE OMITTED

OPTION

-RA: RIGHT ANGLE (SEE FIG. 1 -RA & TABLE 1 SHT. 1)
-SM: SURFACE MOUNT (SEE TABLE 1 SHT. 1 & TABLE 2 SHT. 2)
-LC: LOCKING CLIP (USE LC-05-TM FOR THROUGH HOLE STYLE, SEE FIG. 1, * DIMS) (USE LC-07-TM FOR -SM STYLE, SEE FIG. 3, SHT. 2 * DIMS)
NOT AVAILABLE FOR -RA STYLE
LEAVE BLANK FOR THROUGH HOLE (SEE FIG. 1 & TABLE 1 SHT. 1)
-P: PICK AND PLACE PAD (USE PPP-24, SEE FIG. 4 SHT. 2) (3 POSITION MINIMUM) (NOT AVAILABLE WITH -RA OPTION)
-M: METAL PICK AND PLACE PAD (USE MPP-11, SEE FIG. 5 SHT. 2) (-SM OPTION ONLY) (3 POSITION MINIMUM) (SEE NOTE 8)
(NOT AVAILABLE WITH -RA OPTION)
-TR: TAPE & REEL (SEE FIG. 7 SHT. 3). FOR SM OPTION ONLY.
-K: POLYIMIDE FILM PAD (SEE FIG. 6, SHT. 2) (NOT AVAILABLE WITH -RA OPTION)

ROW SPECIFICATION

-D: DOUBLE (USE STMM-XX-D-LC)

NOTES:

1. MAX PIN ROTATION IN BODY TO BE 2° .
2. PUSHOUT FORCE TO BE 1 lb. MIN.
3. $\odot$ REPRESENTS CRITICAL DIMS.
4. DIMENSIONS IN [] ARE IN MILLIMETERS.
5. FOR LOCKING CLIPS: 12 OZ. MIN RETENTION
6. MEASURE AT BEND.
7. ORIENTATE PINS TO REDUCE THE NUMBER OF BANDOLIER MARKS IN THE POST AREA. (SEE TABLE 4)
8. -M OPTION NOT RECOMMENDED WITH -T OR -TM PLATING OPTIONS FOR LEAD FREE PROCESSING.







FIG. 2

-RA: RIGHT ANGLE

DIFFERENT AS SHOWN OTHERWISE SAME AS FIG. 1

TABLE 1

	LEAD STYLE	"A" REF	"B" REF	"C" REF	PIN A	"L" REF TERMINAL LENGTH	"D" REF	PIN B	"L" REF TERMINAL LENGTH	"D" REF
THROUGH HOLE (SEE FIG. 1)	-01	.100 [2.54]	.092 [2.3]	N/A	T-1S13-04-XX-2	.255 [6.48]	.280 [7.11]	N/A	.255 [6.48]	N/A
	-02	.120 [3.05]	.117 [3.0]	N/A	T-1S13-07-XX-2	.302 [7.67]	.307 [7.80]	N/A	.302 [7.67]	N/A
RIGHT ANGLE (SEE FIG. 2)	-01	.100 [2.5]	.232 [5.9]	.390 [9.9]	T-1S13-05-XX-2	.397 [10.08]	.422 [10.71]	T-1S13-06-X-2	.555 [14.10] REF	.580 [14.73]
	-02	.120 [3.0]	.228 [5.8]	.386 [9.8]	T-1S13-19-XX-2	.413 [10.49]	.438 [11.13]	T-1S13-22-X-2	.571 [14.50] REF	.576 [14.63]
SURFACE MOUNT (SEE FIG. 3)	-01	.100 [2.54]	.172 [4.4]	N/A	T-1S13-07-XX-2	.302 [7.67]	.327 [8.31]	N/A	SEE TABLE 2	N/A
	-02	.120 [3.05]	.173 [4.4]	N/A	T-1S13-20-XX-2	.323 [8.20]	.328 [8.33]	N/A	SEE TABLE 2	N/A



MATERIAL:
BODY: LCP
COLOR: BLACK

TERMINAL:
PHOSPHOR BRONZE

PLOT SCALE: 1= .25

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: KOLB 1-28-92

STMM-1XX-XX-XX-D-XX-XX
SHEET 1 OF 3

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.