

COAXIAL CONNECTOR, SHV, 50 Ohm, Straight panel receptacle, jack (female), flange mount

23_SHV-50-0-2/133_N

Properties

- Suitable for all high voltage applications up to 5 kV DC or 3.5 kV rms
- Used in nuclear instruments or test and measurement equipment
- Voltages are valid for both, the mated and the unmated condition.



Product configuration

Interface type	Gender	Standard
SHV	jack	IEC 60498_MIL-STD-348A/314

Interface and material data

Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data

Impedance	50 Ω
Interface frequency	0.3 GHz

Mechanical data

Weight	0.0143 kg
Mating cycles	500
Flange type	square flange / 17.5 X 17.5
Tab style	solder end

Environmental data

Operation temperature	-65 °C ... 165°C
-----------------------	------------------

Ordering Information Table

Item number	Item description	Packaging type
22542010	23_SHV-50-0-2/133_NE	Single

COAXIAL CONNECTOR, SHV, 50 Ohm, Straight panel receptacle, jack (female), flange mount

23_SHV-50-0-2/133_N

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2718 / Date of publication: 26.11.2023 / uncontrolled copy