

COAXIAL ADAPTER, N - TNC, 50 Ohm, jack / jack (female / female)

31_N-TNC-50-1/133_U

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
N	jack (female)	IEC 61169-16_MIL-STD-348A/304_CECC 22210
TNC	jack (female)	IEC 60169-17_MIL-STD-348A/313_CECC 22200

Interface and material data		
N		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
TNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz
VSWR	DC - 7 GHz ($\leq 1.06 + 0.12 f \text{ GHz}$)

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
7 GHz ... 11 GHz	10 dB	1.9

COAXIAL ADAPTER, N - TNC, 50 Ohm, jack / jack (female / female)
31_N-TNC-50-1/133_U

Mechanical data		
Weight	0.0302 kg	
Mating cycles	500	
Environmental data		
Operation temperature	-65 °C ... 165 °C	
Ordering Information Table		
Item number	Item description	Packaging type
22542392	31_N-TNC-50-1/133_UE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2385 / Date of publication: 27.05.2024 / uncontrolled copy