



## Main

|                                 |                                   |
|---------------------------------|-----------------------------------|
| Range of product                | Harmony XB4                       |
| Product or component type       | Head for pilot light              |
| Product compatibility           | Integral LED                      |
| Device short name               | ZB4                               |
| Bezel material                  | Chromium plated metal             |
| Mounting diameter               | 0.87 in (22 mm)                   |
| Sale per indivisible quantity   | 1                                 |
| Head type                       | Standard                          |
| Shape of signaling unit head    | Round                             |
| Cap/operator or lens colour     | White                             |
| Operator additional information | With grooved lens                 |
| Environmental characteristic    | High ambient lighting environment |

## Complementary

|                                    |                                                                                  |
|------------------------------------|----------------------------------------------------------------------------------|
| CAD overall width                  | 1.14 in (29 mm)                                                                  |
| CAD overall height                 | 1.14 in (29 mm)                                                                  |
| CAD overall depth                  | 1.18 in (30 mm)                                                                  |
| Net Weight                         | 0.06 lb(US) (0.026 kg)                                                           |
| Resistance to high pressure washer | 7000000 Pa at 55 °C, distance : 0.1 m                                            |
| Electrical composition code        | P1 front mounting integral LED<br>P2 front mounting integral LED and transformer |
| Device presentation                | Basic element                                                                    |

## Environment

|                                       |                                                                                                                                         |
|---------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| Protective treatment                  | TH                                                                                                                                      |
| Ambient air temperature for storage   | -40...158 °F (-40...70 °C)                                                                                                              |
| Ambient air temperature for operation | -40...158 °F (-40...70 °C)                                                                                                              |
| Overvoltage category                  | Class I conforming to IEC 60536                                                                                                         |
| IP degree of protection               | IP66 conforming to IEC 60529<br>IP67<br>IP69<br>IP69K                                                                                   |
| NEMA degree of protection             | NEMA 13<br>NEMA 4X                                                                                                                      |
| IK degree of protection               | IK06 conforming to IEC 50102                                                                                                            |
| Standards                             | CSA C22.2 No 14<br>JIS C8201-5-1<br>EN/IEC 60947-1<br>EN/IEC 60947-5-5<br>UL 508<br>EN/IEC 60947-5-1<br>EN/IEC 60947-5-4<br>JIS C8201-1 |

|                      |                                                                                                                                                                                |
|----------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Vibration resistance | 5 gn (f= 2...500 Hz) conforming to IEC 60068-2-6                                                                                                                               |
| Shock resistance     | 30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27<br>50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27 |

## Ordering and shipping details

|                       |                                     |
|-----------------------|-------------------------------------|
| Category              | 22468 - PUSHBUTTONS,22MM(METAL) NEW |
| Discount Schedule     | CS2                                 |
| GTIN                  | 00785901449218                      |
| Nbr. of units in pkg. | 1                                   |
| Package weight(Lbs)   | 0.05 lb(US) (0.02 kg)               |
| Returnability         | Yes                                 |
| Country of origin     | FR                                  |

## Packing Units

|                        |                  |
|------------------------|------------------|
| Unit Type of Package 1 | PCE              |
| Package 1 Height       | 1.57 in (4 cm)   |
| Package 1 width        | 2.05 in (5.2 cm) |
| Package 1 Length       | 1.26 in (3.2 cm) |

## Offer Sustainability

|                            |                                                                                                |
|----------------------------|------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                          |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                              |
| REACH free of SVHC         | Yes                                                                                            |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes                                                                                            |
| Mercury free               | Yes                                                                                            |
| RoHS exemption information | <a href="#">Yes</a>                                                                            |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                         |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                  |
| Circularity Profile        | <a href="#">End Of Life Information</a>                                                        |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|