

COAXIAL ADAPTER, MMBX, 50 Ohm, plug / plug (male / male)

32_MMBX-50-0-2/111_N

Properties

- Smallest board-to-board distance
- Very high frequencies
- Excellent return loss values
- Blind mateable
- Reliable and secure connection



Product configuration		
Interface type	Gender	Standard
MMBX	plug (male)	
MMBX	plug (male)	

Interface and material data		
MMBX		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Bronze	SUCOPRO Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE	
MMBX		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Bronze	SUCOPRO Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	12.4 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 2.5 GHz	32 dB	1.052
2.5 GHz ... 6 GHz	26 dB	1.106
6 GHz ... 12.4 GHz	15 dB	1.433

COAXIAL ADAPTER, MMBX, 50 Ohm, plug / plug (male / male)
32_MMBX-50-0-2/111_N

Mechanical data	
Weight	0.0004 kg
Mating cycles	100

Environmental data	
Operation temperature	-55 °C ... 155 °C

Ordering Information Table		
Item number	Item description	Packaging type
23001750	32_MMBX-50-0-2/111_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2318 / Date of publication: 27.05.2024 / uncontrolled copy