



## D-SUB CONNECTOR CONTACTS



✓ Active

↓ **PRODUCT DRAWING**  
English

↓ **3D PDF**

TE CONNECTIVITY (TE)

### CONTACT,SKT,PWR 8

AMPLIMITE

212014-2

TE Internal Number: 212014-2

Always EU RoHS/ELV Compliant

Contact Type **Socket**

Contact Style **Power**

Contact Size **8**

Contact Base Material **Copper Alloy**

Contact Mating Area Plating Material **Gold over Nickel**

#### Product Drawings

**ASSEMBLY,SOCKET CONTACT POWER VIII,#16 & #18 AWG**

PDF  
English

#### CAD Files

**Customer View Model**

3D\_IGS.ZIP  
English

**Customer View Model**

3D\_STP.ZIP  
English

**Customer View Model**

2D\_DXF.ZIP  
English

**3D PDF**

PDF  
3D

**Customer View Model**

TIF  
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

#### Product Type Features

Insulation Support

**No**

Product Type

**Contact**

Applies To

**Wire/Cable**

#### Body Features

Color Code

**No**

Contact Features	Contact Type	Socket
	Contact Style	Power
	Contact Size	8
	Contact Base Material	Copper Alloy
	Contact Mating Area Plating Material	Gold over Nickel
	Contact Mating Area Plating Thickness (µin)	30
	Solder Tail Contact Plating Thickness (µin)	30
	Solder Tail Contact Plating Material	Gold
Termination Features	Termination Method to Wire/Cable	Crimp
Dimensions	Wire Range	.8 – 1.4 mm² [ 18 – 16 AWG ]
	Insulation Diameter (Max) (mm)	.102
Operation/Application	High Current	No
	For Use With	AMPLIMITE
Packaging Features	Packaging Method	Package
	Packaging Quantity	1
Product Compliance	<a href="#">Statement of Compliance</a> PDF	
	<a href="#">VIEW ALL PRODUCT COMPLIANCE</a>	