

FP 0,8/ 12-MV-SH 8,65 - SMD male connector,
shielded

1154119
<https://www.phoenixcontact.com/us/products/1154119>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



shielded SMD male connector, nominal current: 1.7 A, Test voltage: 500 V AC, number of positions: 12, pitch: 0.8 mm, color: black, contact surface: Au, contact connection type: Pin, mounting: SMD soldering

Your advantages

- Gold-plated contacts ensure transfer quality remains stable over the long term
- Reliable mechanical and electrical connections, thanks to the double-sided ScaleX contact system
- Robustness: ScaleX technology for high tolerance compensation and protection of contacts
- Flexible device design: various numbers of positions, designs, and stack heights with high wipe lengths

Commercial data

Item number	1154119
Packing unit	250 pc
Minimum order quantity	250 pc
Sales key	AA23
Product key	AAWJDE
GTIN	4063151154899
Weight per piece (including packing)	3.376 g
Weight per piece (excluding packing)	3.376 g
Customs tariff number	85366930
Country of origin	CN

FP 0,8/ 12-MV-SH 8,65 - SMD male connector, shielded



1154119

<https://www.phoenixcontact.com/us/products/1154119>

Technical data

Product properties

Product type	shielded SMD male connector
Product family	FP 0,8/...-MV-SH 8,65
Number of positions	12
Pitch	0.8 mm
Number of rows	2
Pin layout	Linear pad geometry
Electrical characteristic	shielded

Data management status

Article revision	01
------------------	----

Electrical properties

Nominal current I_N	1.7 A IEC 60512-5-2:2002-02 (at 20°C 80-pos.)
Contact resistance	25 mΩ
Test voltage	500 V AC IEC 60512-4-1:2003
Electrical characteristic	shielded

Mounting

Mounting type	SMD soldering
Pin layout	Linear pad geometry

Processing notes

Process	Reflow soldering
Moisture Sensitive Level	MSL 1
Classification temperature T_c	260 °C

Material specifications

Material data - contact

Note	WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201
Contact material	Cu alloy
Surface characteristics	Selective coating
Metal surface contact area (top layer)	Gold (Au)
Metal surface contact area (middle layer)	Nickel (Ni)
Metal surface soldering area (top layer)	Tin (Sn)
Metal surface soldering area (middle layer)	Nickel (Ni)

Material data - housing

Color (Housing)	black (9005)
Insulating material	LCP
Insulating material group	IIIb
CTI according to IEC 60112	150

FP 0,8/ 12-MV-SH 8,65 - SMD male connector, shielded



1154119

<https://www.phoenixcontact.com/us/products/1154119>

Flammability rating according to UL 94

V0

Notes

Notes on operation


The permissible voltage during operation depends on the application, taking into consideration the air clearances and creepage distances within the scope of insulation requirements in accordance with IEC 60664-1.

Details for soldering processes

The items are suitable for assembly on both sides and for overhead soldering.

Dimensions

Dimensional drawing



Pitch

0.8 mm

Width [w]

8.7 mm

Height [h]

13.75 mm

Length [l]

6.1 mm

Installed height

13.15 mm

Application

Contact cover

0.8 mm

Center offset

± 0.7 mm in longitudinal and transverse direction

Stack height

13.5 mm Tolerance: +1,5 mm (in combination with Range of articles:FP 0,8/...-FV-SH 4,85)

16.5 mm Tolerance: +1,5 mm (in combination with Range of articles:FP 0,8/...-FV-SH 7,85)

19.5 mm Tolerance: +1,5 mm (in combination with Range of articles:FP 0,8/...-FV 10,85)

19.5 mm Tolerance: +1,5 mm (in combination with Range of articles:FP 0,8/...-FV-SH 10,85)

Wipe length

1.5 mm

Angular tolerance

± 5 ° in longitudinal and transverse direction (when plugging in)

± 5 ° in longitudinal and transverse direction (when plugged in)

Axial offset in X direction (longitudinal)

± 0.3 mm (Tolerance compensation when plugged in)

Axial offset in Y direction (transversal)

± 0.3 mm (Tolerance compensation when plugged in)

PCB design

Pad geometry

0.5 x 1.1 mm

Hole diameter

0.75 mm

Electrical tests

Thermal test | Test group C

Specification

IEC 60512-5-2:2002-02

FP 0,8/ 12-MV-SH 8,65 - SMD male connector, shielded



1154119

<https://www.phoenixcontact.com/us/products/1154119>

Tested number of positions	80
----------------------------	----

Insulation resistance

Specification	IEC 60512-3-1:2002-02
Insulation resistance, neighboring positions	$\geq 5 \text{ G}\Omega$

Air clearances and creepage distances |

Insulating material group	IIIb
Minimum value for clearance and creepage distance	0.25 mm

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 2000 - 10 Hz
Sweep speed	1 octave/min
Amplitude	1.5 mm (10 Hz ... 58 Hz)
Acceleration	200 m/s ² (58 Hz ... 2000 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis

Durability test

Specification	IEC 60512-9-1:2010-03 (following)
Contact resistance R_1	25 m Ω
Contact resistance R_2	25 m Ω
Insertion/withdrawal cycles	500
Insulation resistance, neighboring positions	$\geq 5 \text{ G}\Omega$

Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Semi-sinusoidal
Acceleration	490 m/s ²
Shock duration	11 ms
Test directions	X-, Y- and Z-axis (pos. and neg.)


Ambient conditions

Ambient temperature (operation)	-55 °C ... 125 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Relative humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 100 °C

Packaging specifications

FP 0,8/ 12-MV-SH 8,65 - SMD male connector,
shielded

1154119
<https://www.phoenixcontact.com/us/products/1154119>

Dimensional drawing	
Type of packaging	24 mm wide tape
[W] tape width	24 mm
[W2] coil overall dimension	330 mm
[A] coil diameter	30.4 mm
Outer packaging type	Transparent-Bag
ESD level	(D) electrostatically conductive
Specification	DIN EN 61340-5-1 (VDE 0300-5-1): 2008-07

FP 0,8/ 12-MV-SH 8,65 - SMD male connector, shielded




1154119

<https://www.phoenixcontact.com/us/products/1154119>


Drawings

Diagram



Type: FP 0,8/...-MV-SH 8,65 with FP 0,8/...-FV-SH 10,85 - contacts

Diagram



Type: FP 0,8/...-MV-SH 8,65 with FP 0,8/...-FV-SH 7,85 - contacts


FP 0,8/ 12-MV-SH 8,65 - SMD male connector, shielded



1154119


<https://www.phoenixcontact.com/us/products/1154119>

Diagram



Type: FP 0,8/...-MV-SH 8,65 with FP 0,8/...-FV-SH 10,85 - shroud

Diagram



Type: FP 0,8/...-MV-SH 8,65 with FP 0,8/...-FV-SH 7,85 - shroud

FP 0,8/ 12-MV-SH 8,65 - SMD male connector, shielded



1154119

<https://www.phoenixcontact.com/us/products/1154119>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1154119>



cULus Recognized

Approval ID: E118976-20190703

FP 0,8/ 12-MV-SH 8,65 - SMD male connector, shielded



1154119

<https://www.phoenixcontact.com/us/products/1154119>

Classifications

ECLASS

ECLASS-11.0	27460201
ECLASS-12.0	27460201
ECLASS-13.0	27460201

ETIM

ETIM 9.0	EC002637
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1154119
<https://www.phoenixcontact.com/us/products/1154119>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com