

# IPD PL 3P2,5 M GY - Connector

1088672

<https://www.phoenixcontact.com/us/products/1088672>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, product family: IPD, connection method: Push-lock connection, number of positions: 2+PE, Pin, 0.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, 500 V, 20 A, PA, light gray, coding: P, external cable diameter: 6 mm ... 9 mm and 8 mm ... 13 mm

## Your advantages

- Easy distribution of power, as components are plugged directly
- Simple, time-saving wiring in the field with Push-Lock connection
- Reliable installation in harsh environments with IP66, IP68, and IP69K throughout the entire system
- Secure, tool-free locking even in particularly difficult installation situations
- Fast commissioning with preassembled cable assemblies

## Commercial data

Item number	1088672
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF51
Product key	BF6JAA
GTIN	4055626890890
Weight per piece (including packing)	52.9 g
Weight per piece (excluding packing)	52.9 g
Customs tariff number	85366990
Country of origin	DE

# IPD PL 3P2,5 M GY - Connector



1088672

<https://www.phoenixcontact.com/us/products/1088672>

## Technical data

### Notes

#### General

**NOTE:** Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.

### Product properties

Product type	Installation connector
Product family	IPD
Number of positions	3
Connection profile	2+PE
Position marking	L, N, PE
Number of connections per position	1
Coding	P

#### Data management status

Article revision	00
------------------	----

#### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage (III/3)	6 kV
Rated current	20 A
Rated voltage (III/3)	500 V
Nominal voltage $U_N$	500 V AC
	500 V DC
Nominal current $I_N$	20 A

### Connection data

#### Connection technology

Connection method On the field side	Push-lock connection
-------------------------------------	----------------------

#### Conductor connection

Conductor cross section flexibel	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section solid	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section with ferrule	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Connection cross section AWG	20 ... 14


### Dimensions

# IPD PL 3P2,5 M GY - Connector

1088672

<https://www.phoenixcontact.com/us/products/1088672>



Dimensional drawing	
Width	26.5 mm
Height	26.9 mm
Length	85.9 mm

## Material specifications

Color (Housing)	light gray (RAL 7035)
Material Housing	PA
Material Seal	NBR
Flammability rating according to UL 94	V0
Contact material	Cu
Contact surface material	Ni/Ag/Sn

## Cable/line

External cable diameter	6 mm ... 9 mm
	8 mm ... 13 mm
Position marking	L, N, PE

## Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	50 (IP66/IP68/IP69K)
	100 (IP66)

## Environmental and real-life conditions


Ambient conditions	
Degree of protection	IP66
	IP68 (2 m / 24 h)
	IP69K
	Touch-proof when not plugged in (IP2X)
Impact strength	IK07
Ambient temperature (operation)	-30 °C ... 100 °C
Temperature when conductor connected	-5 °C ... 50 °C
Ambient temperature (storage/transport)	-30 °C ... 100 °C
Resistance to UV radiation	yes

# IPD PL 3P2,5 M GY - Connector


1088672

<https://www.phoenixcontact.com/us/products/1088672>

## Drawings



Derating diagram for 1.5 mm<sup>2</sup>



Derating diagram for 1.0 mm<sup>2</sup>


# IPD PL 3P2,5 M GY - Connector

1088672

<https://www.phoenixcontact.com/us/products/1088672>




Diagram



Derating diagram for 2.5 mm<sup>2</sup>

Dimensional drawing



# IPD PL 3P2,5 M GY - Connector



1088672

<https://www.phoenixcontact.com/us/products/1088672>

## Classifications

### ECLASS

ECLASS-11.0	27440605
ECLASS-13.0	27440605
ECLASS-12.0	27440605

### ETIM

ETIM 9.0	EC002560
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# IPD PL 3P2,5 M GY - Connector



1088672

<https://www.phoenixcontact.com/us/products/1088672>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)