



A Product Line of  
Diodes Incorporated



## SPECIFICATION FOR APPROVAL

|                   |                                                      |
|-------------------|------------------------------------------------------|
| CUSTOMER          | _____                                                |
| NOMINAL FREQUENCY | 27.000000 MHz                                        |
| PRODUCT TYPE      | TYPE HX 2.5×2.0 SEAM SEALED CRYSTAL CLOCK OSCILLATOR |
| SPEC. NO. ( P/N ) | HX2127003Q                                           |
| CUSTOMER P/N      | _____                                                |
| ISSUE DATE        | June 8, 2018                                         |
| VERSION           | B                                                    |

| APPROVED                                                                            | PREPARED                                                                            | QA                                                                                    |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|  |  |  |

### Diodes Incorporated

No.2, Ziqiang 5th Rd., Zhongli Industrial Park,  
Zhongli Dist., Taoyuan City 32063, Taiwan (R.O.C.)  
TEL: 886-3-451-8888  
FAX: 886-3-461-3865  
<https://www.diodes.com>

\*Pb-free  
\*RoHS Compliant  
\*HF-Halogen Free  
\*REACH Compliant  
\*AEC-Q200 Compliant

## TYPE HX 2.5×2.0 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

**HX2127003Q**

VER. B      8-Jun-18

## VERSION HISTORY

[illegible]

# TYPE HX 2.5×2.0 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

## HX2127003Q

VER. B 8-Jun-18

### ELECTRICAL SPECIFICATIONS

SRe Part Number : HX2127003Q

| Item                            | Symbol                         | Specifications      | Units | Notes                              |
|---------------------------------|--------------------------------|---------------------|-------|------------------------------------|
| Nominal Frequency               | F <sub>0</sub>                 | 27.000000           | MHz   |                                    |
| Frequency Stability             | FT                             | ± 20                | ppm   | **See note                         |
| Operating Temperature Range     | TR                             | -40 to +105         | °C    |                                    |
| Supply Voltage                  | V <sub>DD</sub>                | +2.8 ± 5.0%         | V     |                                    |
| Logic Type                      | LT                             | LVC MOS             |       |                                    |
| Supply Current, Output Enabled  | I <sub>DD</sub> /OE            | 20                  | mA    | Max                                |
| Supply Current, Output Disabled | I <sub>DD</sub> /OD            | 100                 | μA    | Max                                |
| Duty Cycle (Symmetry)           | DC/SY                          | 45 / 55             | %     | Measured 50% of Waveform           |
| Rise / Fall Time                | T <sub>R</sub> /T <sub>F</sub> | 3                   | ns    | Max. measured 20 / 80% of Waveform |
| Output Voltage "0" Level        | V <sub>OL</sub>                | 10% V <sub>DD</sub> | V     | Max                                |
| Output Voltage "1" Level        | V <sub>OH</sub>                | 90% V <sub>DD</sub> | V     | Min                                |
| Output Load                     | CL                             | 15                  | pF    | Max                                |
| Jitter, Phase                   | RMS                            | 1                   | ps    | Max. 12kHz ~ 5MHz Frequency Band   |
| Jitter, Accumulated             | RMS(1-σ)                       | 4                   | ps    | Max. 20,000 Consecutive Periods    |
| Jitter, Peak to Peak            | Pk-Pk                          | 40                  | ps    | Max. 100,000 Random Periods        |
| Start Up Time                   |                                | 5                   | ms    | Max.                               |
| Storage Temperature Range       |                                | -55 to +125         | °C    |                                    |

※ This product doesn't include harmful substance that stipulated by SONY SS-00259 Level 1 and S-AT2-001 Level 1 standard. RoHS Compliant (Pb - Free).

\*\*Stability includes all combinations of Operating Temperature, Load changes, rated Input (Supply) Voltage changes, Initial Calibration Tolerance (25°C), Aging (1 year at 25°C Average Effective Ambient Temperature), Shock and Vibration.

#### Output Enable / Disable Function


| Parameter                                                | Min.               | Typ. | Max.               | Units | Notes          |
|----------------------------------------------------------|--------------------|------|--------------------|-------|----------------|
| Input Voltage (Pin1), Output Enable                      | 0.7V <sub>DD</sub> |      |                    | V     | Or Open        |
| Input Voltage (Pin1), Output Disable (low power standby) |                    |      | 0.3V <sub>DD</sub> | V     | Output is Hi-Z |
| Internal Pullup Resistance                               | 30                 |      |                    | KΩ    |                |
| Output Disable Delay                                     |                    |      | 50                 | ns    |                |

# TYPE HX 2.5×2.0 SEAM SEALED CRYSTAL CLOCK OSCILLATOR


**HX2127003Q**

VER. B 8-Jun-18

## TEST CIRCUIT



## OUTPUT WAVEFORM



# TYPE HX 2.5×2.0 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

**HX2127003Q**

VER. B 8-Jun-18

## AEC-Q200 RELIABILITY TEST SPECIFICATIONS:

### 1. Initial

- 1.1 Physical Dimensions: JESD22, Method JB1-100
- 1.2 External Visual: MIL-STD-883, Method 2009
- 1.3 Freq. Vs. Temperature: Per Specification/Datasheet

### 2. Mechanical


- 2.1 Mechanical Shock: MIL-STD-202 Method 213
- 2.2 Vibration: MIL-STD-202 Method 204
- 2.3 Solderability: J-STD-002
- 2.4 Board Flex: AEC Q200-005
- 2.5 Terminal Strength (SMD): AEC Q200-006

### 3.Environmental

- 3.1 Temp Cycle: JESD22, Method JA-104
- 3.2 Resistance to Solder Heat: MIL-STD-202 Method 210
- 3.3 High Temperature Operating Life: MIL-STD-202, Method 108
- 3.4 High Temp Exposure: MIL-STD-202, Method 108
- 3.5 High Temp & High Humidity: MIL-STD-202, Method 103
- 3.6 Thermal Shock: MIL-STD-202, Method 107

## SUGGESTED IR REFLOW PROFILE

\*As per IPC-JEDEC J-STD-020D



Note:


|   | Stage        | Temperature | Time       |
|---|--------------|-------------|------------|
| A | Preheat      | 150~200°C   | 60~120 Sec |
| B | Primary Heat | 217°C       | 60~150 Sec |
| C | Peak         | 260°C       | 10 Sec     |

# TYPE HX 2.5×2.0 SEAM SEALED CRYSTAL CLOCK OSCILLATOR


**HX2127003Q**

VER. B 8-Jun-18


## MARKING



## MECHANICAL DRAWINGS ( Scale:None. Dimensions are in mm.)



### Recommended Land Pattern\*



\*External high-frequency power decoupling is recommended.(see test circuit for minimum recommendation). To ensure optimal performance, do not route traces beneath the package.


| Pin | Function        |
|-----|-----------------|
| 1   | OE              |
| 2   | Ground          |
| 3   | Clock Output    |
| 4   | V <sub>DD</sub> |

# TYPE HX 2.5×2.0 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

**HX2127003Q**

VER. B 8-Jun-18

## TAPE & REEL



1. 230mm minimum leader which consist of carrier and/or tape followed by a minimum of 160mm of empty carrier tape sealed with cover tape.
2. 160mm minimum trailer of empty carrier tape sealed with cover tape.

# TYPE HX 2.5×2.0 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

**HX2127003Q**

VER. B 8-Jun-18

## PACKING

