

COAXIAL CONNECTOR, BMA, 50 Ohm, Straight panel cable jack (female), flange mount

25_BMA-50-3-2/119_N

Properties

- Offers a range of floating configurations
- High reliability and ease of assembly
- Intermatable with the OSP connectors series
- Applicable in frequencies up to 18 GHz



Product configuration

Interface type	Gender	Standard
BMA	jack	IEC 60169-33_MIL-STD-348A/321

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PFA / PTFE	

Electrical data

Impedance	50 Ω
Interface frequency	18 GHz

Mechanical data

Weight	0.0054 kg
Mating cycles	1000
Cable entry centre contact	plugged
Cable entry outer contact	soldered

Environmental data

Operation temperature	-65 °C ... 125 °C
-----------------------	-------------------

Ordering Information Table

Item number	Item description	Packaging type
22645605	25_BMA-50-3-2/119_NE	Single

COAXIAL CONNECTOR, BMA, 50 Ohm, Straight panel cable jack (female), flange mount

25_BMA-50-3-2/119_N

Suitable cables	
Cable group	Y5 - 3 mm / 50 Ohm
	Y17 - 3 mm / 50 Ohm
	Y12 - 3 mm / 50 Ohm
Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2519 / Date of publication: 18.06.2024 / uncontrolled copy