

COAXIAL ADAPTER, N - QN, 50 Ohm, plug / plug (male / male)

32_N-QN-50-1/133_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
N	plug (male)	IEC 61169-16_MIL-STD-348A/304_CECC 22210
QN	plug (male)	QN QLF compliant

Interface and material data		
N		
Piece parts	Material	Plating
Centre contact	Brass	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
QN		
Piece parts	Material	Plating
Centre contact	Brass	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 4 GHz	35 dB	1.035
4 GHz ... 8 GHz	30 dB	1.06

COAXIAL ADAPTER, N - QN, 50 Ohm, plug / plug (male / male)
32_N-QN-50-1/133_N

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
8 GHz ... 10 GHz	20 dB	1.22
Mechanical data		
Weight	0.0288 kg	
Mating cycles	500	
Environmental data		
Operation temperature	-40 °C ... 125 °C	
Ordering Information Table		
Item number	Item description	Packaging type
23033962	32_N-QN-50-1/133_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2301 / Date of publication: 27.05.2024 / uncontrolled copy