


SENCITY® Omni-S LTE 800 + GNSS Antenna

1399.19.0006

Properties

- Omnidirectional Cellular/LTE and GNSS antenna
- Supports 2G, 3G, 4G LTE 800 MHz up to LTE 2600 MHz
- Cellular/LTE (EUR) vertical polarized radiator for SISO scenario on one port
- Circular polarized GNSS antenna with LNA on second port
- Single hole cabinet mounting, for outdoor & indoor applications
- Vandalism proof "IK10" acc. to IEC 62262/2002-02



Electrical bands				
	Band 1	Band 2	Band 3	Band 4
Name				
Frequency	790 MHz ... 930 MHz	930 MHz ... 960 MHz	1710 MHz ... 2170 MHz	2300 MHz ... 2690 MHz
VSWR	2	2.5	1.7	1.7
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
Gain	2 dBi	2 dBi	6 dBi	4 dBi
Ambient Temperature	25 °C	25 °C	25 °C	25 °C
Composite Power max	60 W	60 W	50 W	40 W

	Band 5
Name	GNSS
Frequency	1559 MHz ... 1610 MHz
VSWR	1.8
Impedance	50 Ω
Gain	
Ambient Temperature	
Composite Power max	

SENCITY® Omni-S LTE 800 + GNSS Antenna

1399.19.0006

Electrical remarks	
Remarks	GROUND PLANE: Antenna works on metallic as well as on non-metallic ground plane. VSWR is valid for both mounting options; GAIN VALUES: Indicated gain values are valid for non-metallic ground plane. Gain of this antenna on metallic surface is higher for 790 to 960 MHz: 3.5 dBi (instead of 2 dBi)

Ports		
	Port 1	Port 2
Port name	Cellular/LTE	GNSS
Connector	SMA, plug (male)	SMA, plug (male)
Cable type	ENVIROFLEX_316_D	ENVIROFLEX_316_D
Cable length	1 m	1 m
Polarization	vertical	circular right
DC grounded	No	No

Connections		
Port number	Port 1	Port 2
Band 1	✓	
Band 2	✓	
Band 3	✓	
Band 4	✓	
Band 5		✓

Electrical data LNA	
LNA is connected to	Port 2
Input voltage	3 V ... 5 V
Current consumption	30 mA
Noise figure	2 dB
Gain	30 dB
Total gain @90° elevation	30 dBic
Remarks	Values for LNA power consumption, noise figure and gain are given for a 5V operating voltage and may differ slightly for a lower voltage

Mechanical data	
Weight	0.35 kg
Dimensions	33.2 mm x 145 mm (Height x Diameter)

Interface and material data	
Radome material	PC (Polycarbonate)
Radome colour	RAL 7044 (grey)

Environmental data	
Operation temperature	-55 °C ... 85 °C
Storage temperature	-55 °C ... 85 °C
Transport temperature	-55 °C ... 85 °C
Environment (application)	Outdoor
Flammability rating	UL 94-V0


SENCITY® Omni-S LTE 800 + GNSS Antenna

1399.19.0006

Environmental remarks
INGRESS PROTECTION: IP 66, IP67 AND IP 69K when mounted on cabinet's flat surface or roof - IP 66 and IP67 when mounted on bracket with sealed cable conduit TEMPERATURE RANGE: EN 60068-2-1 (2007), test Ab, -55°C, 16h and EN-60068-2-2 (2007), test Bb, +85°C, 16h THERMAL SHOCK: IEC 60068-2-14 (2009), test Na, -55°C to +85°C, 3h, 5 cycles SOLAR RADIATION: EN 60068-2-5, test Sa, procedure B, 1200 W/m2, 3 x 24h RELATIVE HUMIDITY: EN 60068-2-78 (2012), test Cb, RH 95%, 21d (damp heat, steady state) RELATIVE HUMIDITY: EN 60068-2-30 (2005), RH 97%, 6 cycles (damp heat, cyclic) SALT SPRAY: EN 60068-2-11 (2002), test Ka, 96h MECHANICAL VIBRATIONI / SHOCK: IEC 61373 (1999), § 9 and § 10, category 2 VANDALISM: EN 60068-2-75 (1997), IEC 62262 (2002) IK10, test Ehc CORROSION: MIL-F-14072 E type 1 "exposed"

Additional Information
This product can be customized alternatively in the following way: - Cable length from 300 to 5000 mm - Choice of RF connector (SMA, R-SMA, QMA, TNC, R-TNC, N) - Customer specific port labeling on pigtails - Further wireless bands, e.g. dual-band WiFi MIMO or Cellular/LTE SISO

Outline drawing



HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3244 / Date of publication: 18.06.2024 / uncontrolled copy