

# FOC-TRX-SFP+-10G-SR-ET - Transceiver



1334214

<https://www.phoenixcontact.com/us/products/1334214>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multimode SFP+ transceiver for transmission up to 10 Gbps over 500 m at wavelengths of 850 nm in the extended temperature range

## Your advantages

- Maximum flexibility, thanks to the non-proprietary multi-source agreement (MSA)
- Superior system availability, thanks to Plug and Play during operation
- Future-proof, thanks to RoHS 2 conformity
- Maximum data transmission quality
- Interference-free data transmission, even for EMC-sensitive applications
- Reliable data transmission in the extended temperature range

## Commercial data

Item number	1334214
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNJAC
GTIN	4063151633516
Weight per piece (including packing)	34.9 g
Weight per piece (excluding packing)	34.9 g
Customs tariff number	85176200
Country of origin	TW

# FOC-TRX-SFP+-10G-SR-ET - Transceiver



1334214

<https://www.phoenixcontact.com/us/products/1334214>

## Technical data

### Dimensions

Width	13.7 mm
Height	13 mm
Length	57.3 mm

### Material specifications

Housing material	Metal
------------------	-------

### Interfaces

Transmission speed	10 Gbps
Wavelength	850 nm

### Product properties

Product type	SFP module
Type	SFP Modul
Connection profile	LC-Duplex
Type of packaging	Box packaging

### Data management status

Article revision	00
------------------	----

### Electrical properties

Transmission speed	10 Gbps
--------------------	---------

### Connection data

Connection method	To insert in SFP slot
-------------------	-----------------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 55 °C

### Standards and regulations

Laser class	1
-------------	---

# FOC-TRX-SFP+-10G-SR-ET - Transceiver



1334214

<https://www.phoenixcontact.com/us/products/1334214>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1334214>



**cULus Recognized**

Approval ID: E140403-20100913

# FOC-TRX-SFP+-10G-SR-ET - Transceiver



1334214

<https://www.phoenixcontact.com/us/products/1334214>

## Classifications

### ECLASS

ECLASS-11.0	27440392
ECLASS-12.0	27440392
ECLASS-13.0	27440392

### ETIM

ETIM 9.0	EC002943
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# FOC-TRX-SFP+-10G-SR-ET - Transceiver



1334214  
<https://www.phoenixcontact.com/us/products/1334214>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)