

Features

- Proprietary α SiC™ MOSFET technology
- Low loss, fast switching speeds with low R_g
- Optimized drive voltage ($V_{GS} = 15\text{V}$) for broad driver compatibility
- Robust body diode and low Q_{rr}

Applications

Renewable

- EV Charger
- Solar Inverters

Industrial

- UPS
- SMPS
- Motor Drives


Product Summary

V_{DS} @ T_J, max	1200 V
I_{DM}	120A
$R_{DS(ON)}$, typ	33 m Ω
Q_{rr}	226 nC
E_{oss} @ 800V	63 μJ
100% UIS Tested	





Pin Configuration

Top View



Bottom View



Ordering Part Number	Package Type	Form	Shipping Quantity
AOM033V120X2	TO-247-4L	Tube	30/Tube

Absolute Maximum Ratings

(TA = 25°C, unless otherwise noted)

Symbol	Parameter		AOM033V120X2	Units
V_{DS}	Drain-Source Voltage		1200	V
$V_{GS, \text{MAX}}$	Gate-Source Voltage	Maximum	-8/+18	V
$V_{GS,\text{OP,TRANS}}$		Max Transient ^(A)	-8/+20	
$V_{GS,\text{OP}}$		Recommended Operating ^(B)	-5/+15	
I_D	Continuous Drain Current	$T_C = 25^\circ\text{C}$	68	A
		$T_C = 100^\circ\text{C}$	48	
I_{DM}	Pulsed Drain Current ^(C)		120	
E_{AS}	Single Pulsed Avalanche Energy ^(D)		1000	mJ
P_D	Power Dissipation ^(C)		300	W
T_J, T_{STG}	Junction and Storage Temperature Range		-55 to 175	°C
T_L	Maximum lead temperature for soldering purpose, 1/8" from case for 5 seconds		300	°C

Thermal Characteristics

Symbol	Parameter	AOM033V120X2	Units
R _{θJA}	Maximum Junction-to-Ambient ^(E,F)	40	°C/W
R _{θJC}	Maximum Junction-to-Case ^(G)	0.5	°C/W

Electrical Characteristics

(T_A = 25°C, unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
STATIC PARAMETERS						
BV _{DSS}	Drain-Source Breakdown Voltage	I _D =250 µA, V _{GS} =0V, T _J =25°C I _D =250 µA, V _{GS} =0V, T _J =150°C	1200			V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} =1200V, V _{GS} =0V, T _J =25°C			100	µA
I _{GSS}	Gate-Body Leakage Current	V _{DS} =0V, V _{GS} =+15/-5V			±100	nA
V _{GS(th)}	Gate Threshold Voltage	V _{DS} = V _{GS} , I _D =17.5 mA		2.8		V
R _{DS(ON)}	Static Drain-Source On-Resistance	V _{GS} =15V, I _D =20A T _J =25°C T _J =150°C	33	43	mΩ	
g _{FS}	Forward Transconductance	V _{DS} =20V, I _D =20A		15	-	S
V _{SD}	Diode Forward Voltage	I _S =17.5A, V _{GS} =-5V		4	5	V
DYNAMIC						
C _{iss}	Input Capacitance	V _{GS} =0V, V _{DS} =800V, f=1 MHz		2908		pF
C _{oss}	Output Capacitance			128		pF
C _{rss}	Reverse Transfer Capacitance			9.9		pF
E _{oss}	Cross Stored Energy			63		µJ
R _G	Gate Resistance	f=1 MHz		1.7		Ω
SWITCHING						
Q _g	Total Gate Charge	V _{GS} =-5/+15V, V _{DS} =800V, I _D =20A, I _{GS} =50 mA		104		nC
Q _{gs}	Gate Source Charge			37		nC
Q _{gd}	Gate Drain Charge			32		nC
t _{d(on)}	Turn-On Delay Time	V _{GS} =-5V/+15V, V _{DS} =800V, I _D =40A, R _G =2Ω L=60 µH FWD: AOM033V120X2		13.3		ns
t _r	Turn-On Rise Time			15.4		ns
t _{d(off)}	Turn-Off Delay Time			15.3		ns
t _f	Turn-Off Fall Time			5.1		ns
E _{on}	Turn-On Energy			297		µJ
E _{off}	Turn-Off Energy			40		µJ
E _{tot}	Total Switching Energy	I _F =20A, dI/dt=1500A/us, V _{GS} =-5V, V _{DS} =800V		337		µJ
t _{rr}	Body Diode Reverse Recovery Time			48		ns
I _{rm}	Peak Reverse Recovery Current			13		A
Q _{rr}	Body Diode Reverse Recovery Charge			226		nC

Notes:

- A. t_{pulse} < 1 µs, f > 1 Hz
- B. Device can be operated at V_{GS}=0/15V. Actual operating V_{GS} will depend on application specifics such as parasitic inductance and dV/dt but should not exceed maximum ratings.
- C. The power dissipation P_D is based on T_{J(MAX)}=175°C, using junction-to-case thermal resistance, and is more useful in setting the upper dissipation limit for cases where additional heatsinking is used.
- D. L=5mH, I_S=20A, R_G=25Ω, Starting T_J=25°C.
- E. The value of R_{θJA} is measured with the device in a still air environment with T_A = 25°C.

- F. The R_{θJA} is the sum of the thermal impedance from junction to case R_{θJC} and case to ambient.
- G. The value of R_{θJC} is measured with the device mounted to a large heatsink, assuming a maximum junction temperature of T_{J(MAX)}=175°C.
- H. The static characteristics in Figures 1 to 8 are obtained using <300 ms pulses, duty cycle 0.5% max.
- I. These curves are based on R_{θJC} which is measured with the device mounted to a large heatsink, assuming a maximum junction temperature of T_{J(MAX)}=175°C. The SOA curve provides a single pulse rating.

Typical Electrical and Thermal Characteristics




Figure 1. On-Region Characteristics $T_J = 25^\circ\text{C}$




Figure 2. On-Region Characteristics $T_J = 175^\circ\text{C}$




Figure 3. On-Resistance vs. Junction Temperature




Figure 4. Normalized On-Resistance vs. Junction Temperature




Figure 5. Transfer Characteristics




Figure 6. Threshold Voltage vs. Junction Temperature

Typical Electrical and Thermal Characteristics (Continued)




Figure 7. Body-Diode Characteristics at 25°C




Figure 8. Body-Diode Characteristics at 175°C




Figure 9. Gate-Charge Characteristics




Figure 10. Capacitance Characteristics




Figure 11. C_{ooss} Stored Energy




Figure 12. Switching Energy vs. Drain Current

Typical Electrical and Thermal Characteristics (Continued)




Figure 13. Switching Energy vs. Drain Current




Figure 14. Turn-On Energy and dV/dt vs. External Gate Resistance




Figure 15. Power Derating vs. Case Temperature (Note I)




Figure 16. Current Derating vs. Case Temperature (Note I)




Figure 17. Maximum Forward Biased Safe Operating (Note I)

Typical Electrical and Thermal Characteristics (Continued)




Figure 18. Normalized Maximum Transient Thermal Impedance for AOM033V120X2 (Note I)

Test Circuits and Waveforms




Figure 19. Gate Charge Test Circuits and Waveforms




Figure 20. Inductive Switching Test Circuit and Waveforms




Figure 21. Unclamped Inductive Switching (UIS) Test Circuit and Waveforms





Figure 22. Diode Recovery Test Circuits and Waveforms

Package Dimensions, TO-247-4L




TOP VIEW

SIDE VIEW

BOTTOM VIEW



SIDE VIEW




RECOMMENDED THROUGH HOLES
FOR LAND PATTERN

NOTE:

1. CONTROLLED DIMENSIONS ARE IN MILLIMETERS.
2. THIS IS AN ENGINEERING DRAFT FOR REVIEW. AOS CONFIDENTIAL.

SYMBOLS	DIM. IN MM			DIM. IN INCH		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	4.90	5.00	5.10	0.193	0.197	0.201
A1	2.32	2.42	2.52	0.091	0.095	0.099
A2	1.90	2.00	2.10	0.075	0.079	0.083
b	1.17	1.22	1.27	0.046	0.048	0.050
b1	1.20	1.30	1.40	0.047	0.051	0.055
b2	1.31	1.41	1.51	0.052	0.056	0.059
b3	2.45	2.65	2.85	0.096	0.104	0.112
b4	1.31	1.41	1.51	0.052	0.056	0.059
b5	2.45	2.65	2.85	0.096	0.104	0.112
c	0.57	0.62	0.67	0.022	0.024	0.026
D	20.80	20.95	21.10	0.819	0.825	0.831
D1	16.25	16.55	16.85	0.640	0.652	0.663
D2	1.00	1.15	1.30	0.039	0.045	0.051
E	15.77	15.92	16.07	0.621	0.627	0.632
E1	13.43	13.63	13.83	0.529	0.536	0.544
E2	4.29	4.39	4.49	0.169	0.173	0.177
E3	1.70	1.80	1.90	0.067	0.071	0.075
e	2.54BSC			0.1000BSC		
e1	5.08BSC			0.2000BSC		
N	4			4		
L	19.82	20.02	20.22	0.780	0.788	0.796
L1	4.01	4.21	4.41	0.158	0.166	0.174
P	3.50	3.60	3.70	0.138	0.142	0.146
P1	7.00	7.20	7.40	0.276	0.283	0.291
Q	5.65	5.75	5.85	0.222	0.226	0.230
S	6.07	6.17	6.27	0.239	0.243	0.247

Part Marking



LEGAL DISCLAIMER

Applications or uses as critical components in life support devices or systems are not authorized. AOS does not assume any liability arising out of such applications or uses of its products. AOS reserves the right to make changes to product specifications without notice. It is the responsibility of the customer to evaluate suitability of the product for their intended application. Customer shall comply with applicable legal requirements, including all applicable export control rules, regulations and limitations.

AOS' products are provided subject to AOS' terms and conditions of sale which are set forth at:
http://www.aosmd.com/terms_and_conditions_of_sale

LIFE SUPPORT POLICY

ALPHA AND OMEGA SEMICONDUCTOR PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS.

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.