

# HC-STA-B10-SHWS-2SSM40-ELC-AL - Housing



1082580

<https://www.phoenixcontact.com/us/products/1082580>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surface mounting housing B10, with single locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 2, lateral, 2x M40, height: 74.5 mm, cable gland: none, Standard

## Your advantages

- Good shielding in the event of electromagnetic interference

## Commercial data

Item number	1082580
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF56
Product key	BF7APB
Catalog page	Page 605 (C-2-2019)
GTIN	4055626816197
Weight per piece (including packing)	254.8 g
Weight per piece (excluding packing)	254.8 g
Customs tariff number	85389099
Country of origin	CN

# HC-STA-B10-SHWS-2SSM40-ELC-AL - Housing



1082580

<https://www.phoenixcontact.com/us/products/1082580>

## Technical data

### Notes

General	For contact inserts HC-B10, BB18, DD42, M, K8/24
---------	--


### Product properties

Product type	Housing with locking latch
Housing type	Surface mounting housing
Application	Standard
Type	B10
No. of cable outlets	2
Type of the screw connection	2x M40
Type	Tall design
Cable outlet	lateral
Pg screw connection	none

### Data management status

Article revision	03
------------------	----

### Dimensions

Dimensional drawing	
Width	52 mm
Height	74.5 mm
Length	92 mm
Hole diameter	5.5 mm

### Material specifications

Flammability rating according to UL 94	V0 (Interlock)
Seal material	NBR, conductive
Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated
Locking latch material	PA

### Mechanical properties

#### Mechanical data

Type of the screw connection	2x M40
Locking type	Latch

### Connection data

# HC-STA-B10-SHWS-2SSM40-ELC-AL - Housing



1082580

<https://www.phoenixcontact.com/us/products/1082580>

Tightening torque	2 Nm ... 3 Nm (for M5 mounting screws on the surface-mount housing)
-------------------	---

## Mounting

Assembly note	One opening is sealed with a plastic filler plug and can be opened using a screwdriver.
---------------	---

## Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 125 °C

# HC-STA-B10-SHWS-2SSM40-ELC-AL - Housing




1082580

<https://www.phoenixcontact.com/us/products/1082580>

## Drawings

Dimensional drawing



Dimensional drawing

# HC-STA-B10-SHWS-2SSM40-ELC-AL - Housing




1082580

<https://www.phoenixcontact.com/us/products/1082580>


## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1082580>




DNV

Approval ID: TAE000037S




cUL Recognized

Approval ID: E255026



UL Recognized

Approval ID: E255026



cULus Recognized

# HC-STA-B10-SHWS-2SSM40-ELC-AL - Housing



1082580

<https://www.phoenixcontact.com/us/products/1082580>

## Classifications

### ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

### ETIM

ETIM 9.0	EC000437
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# HC-STA-B10-SHWS-2SSM40-ELC-AL - Housing



1082580

<https://www.phoenixcontact.com/us/products/1082580>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)